

# Belden Monitor Specification

## 9318-0500 – Compact Climate Monitor



---

Internal Temperature Sensor	-20 to 85 C; +/- .3C
Relative Humidity	0 to 100% RH; +/- 2%
Ethernet Connection	RJ45
Remote Sensor Inputs	2
Power	6 – 18 VDC
Network Protocols Supported & Data Access Formats	DHCP, HTTP, HTTPS(SSL/TLS), ICMP, TCP/IP, SMTP/POP3 & HTML, SNMP, CSV/Plain Text, Telnet WAP, PDA Formatted HTML, XML
Made in the USA	Yes
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Chassis Dimensions (LxHxD)	5.25" x 1.75" x 1.5"
Unit Weight	1

**To insure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.**

Company: \_\_\_\_\_

Authorized  
Customer Signature: \_\_\_\_\_ Date: \_\_\_\_\_