

## Part Number 9318-0501

### Temperature Sensor

Add remote temperature sensors to your Monitor or compatible PDU to monitor critical areas



#### Features

- Plug-n-Play
- Small and Lightweight
- Waterproof

#### Description

This sensor allows you to monitor remote temperatures. Reporting back to the appliance in real-time, you can configure alarms to receive email, email-to-SMS and SNMP trap notifications when specified thresholds are breached. The sensor is suitable for a wide range of applications including monitoring of critical IT infrastructure, cold storage monitoring and more. The standard temperature probe measures 1.25" (3.18 cm) in length. A 4" (10.16 cm) and 10" (25.4 cm) probe option is available for customers wanting to submerge these probes in water or glycol for liquid temperature monitoring.

#### Specifications

Temperature	
Range	-55°C to +125°C (-67°F to +257°F)
Accuracy	± 0.5°C, -10°C to +85°C
Connection	RJ-12, 6p6C Cat-3
Dimensions	12', 20', 50', 100' and Custom
Ingress Protection Rating	1P67- Waterproof
	SAE- 316 Stainless Steel
Notes	Maximum aggregate cable length of digital sensors is 600' per appliance
Warranty	1 Year

**To insure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.**

Company: \_\_\_\_\_

Authorized  
Customer Signature: \_\_\_\_\_ Date: \_\_\_\_\_