

Belden PDU Specification

9318-0503 – 12ft Cord

9318-0515 – 20ft Cord

9318-0516 – 50ft Cord

Description:

(Remote Temperature, Airflow, Humidity, Dew Point) is an all-in-one sensor providing multiple remote environment readings as a complete package.

- Provides measurements for temperature, humidity, air flow and dew point
- Accurate and compact, easy to install
- Compatible devices support up to 4 or 16 sensors, depending on model
- Get alerts via email, SNMP and/or phone call*



A plastic tube contains the sensors and supporting circuitry. Connects to a digital port.

Specification:

Temperature:

Normal operating range: 5 to 60 °C (41 to 140 °F),

20-80% RH

Maximum Operating Range: -40 to 85 °C (-40 to 185 °F), 0-100% RH

Accuracy: +/-0.5 °C (0.9 °F), +/-2% RH (over normal operating range)

+/-1 °C(1.8 °F) and +/-5% RH (outside of normal operating range)

Humidity: Normal operating range: 20% to 80% RH

Accuracy (normal range): +/- 2% RH at 25°C

Extended range: 0% to 100% RH

Dew Point: -40 to 185 °F (-40 to 85 °C)

Air Flow: 0 to 100 (relative value)

Cable type: Cat-3 with RJ-12 connector

Cable length: 12', 20', 50', 100' or custom

Warranty: 1 year

To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized

Customer Signature: _____ Date: _____