

**9318-0535 (120V)**  
**9318-0545 (220V)**

### Photoelectric Smoke Alarm

- Detect smoke in your server room



Photoelectric Smoke Alarm for 120VAC/9VDC and 220VAC/9VDC Single or Multiple (Tandem) Station and Specialty Applications

120VAC and 220VAC photoelectric smoke alarm/detector with 9VDC battery back-up as an auxiliary power source in the event of an electrical failure. Features a warning signal for low or missing battery, and a dry-contact relay output suitable for use with any Belden Climate Monitor with analog inputs.

- 120VAC and 220VAC with 9VDC battery back-up
- Low or missing battery indicator
- 9VDC alkaline battery included
- Patented three-position test switch
- Includes 90db piezo solid state non-latching horn
- Tandem connection up to 12 units; 6 on relay models
- Nominal 3.0% sensitivity
- 5:1 signal-to-noise ratio
- Pulsing LED sensing chamber
- Fully insect-screened
- Solid State LED condition indicator
- Quick-disconnect wiring harness
- Mounting hardware adapts to standard junction boxes
- Protective high air velocity gasket
- On-site maintenance washing program (EasyWash™)
- Compliant with NFPA Standards
- Temporal 3 Evacuation Sounding Device (9123 and 9223)

**To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.**

Company: \_\_\_\_\_

Authorized

Customer Signature: \_\_\_\_\_ Date: \_\_\_\_\_