


# Belden PDU Specification

**9318-0518 (10' Cord)**  
**9318-0557 (50' Cord)**

## Description:

The digital sensor collects and transmits real-time temperature, humidity and dew point data to protect critical data center equipment from heat and moisture. This model offers two RJ12 ports, an uplink port to connect to a host device and a supplementary input for daisy-chaining.

The digital sensor requires a host device to transmit data. It counts as a single digital sensor while reporting multiple temperature readings. The plastic enclosure mounts easily anywhere in the data center with screws, magnets or adhesive.



## Sensor Details:

- Temperature Range: -4 °F to 176 °F (-20 °C to 80 °C) +/-0.5 °C
- Humidity: 5% to 95%, +/-3%
- Dew point: -58 °F to 185 °F (-50 °C to 85 °C)

**To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.**

Company: \_\_\_\_\_

Authorized

Customer Signature: \_\_\_\_\_ Date: \_\_\_\_\_