



**DCXS Series Standard Configuration Options**

**SERIES/FRAME STYLE** - DCXS (84h x 36w x 15d) SEISMIC

**CBL FLOW** - \_\_DIRECTION

- 1 - LEFT TO RIGHT
- 2 - RIGHT TO LEFT

**COLOR\*** -

- 1 - CENTRAL OFFICE WHITE
- 2 - BLACK

**TOP PANEL** -

- 0 - NONE (ALL KNOCKOUTS REMOVED)
- 1 - BLANK (ALL KNOCKOUTS IN PLACE)
- 2 - BRUSH + (4) TOP CABLE BRACKETS
- 3 - BRUSH + (8) TOP CABLE BRACKETS

**BOTTOM PANEL** -

- 0 - NONE (ALL KNOCKOUTS REMOVED)
- 1 - BLANK (ALL KNOCKOUTS IN PLACE)
- 2 - BRUSH + (4) BOT CABLE BRACKETS
- 3 - BRUSH + (8) BOT CABLE BRACKETS

**DOORS\*\*** -

- 0 - NONE
- 1 - BI-FOLD PLEXIGLASS
- 2 - BI-FOLD PERFORATED
- 3 - BI-FOLD SOLID

**SIDE PANEL** -

- 0 - NONE
- 1 - PLEXIGLASS
- 2 - SOLID

**REAR PANEL** -

- 0 - NONE
- 1 - SOLID
- 2 - CABLE MANAGEMENT

**HOUSING CABLE ATTACHMENT** -

- 0 - NONE
- 1 - 4 CABLE DIST BRACKETS
- 2 - 8 CABLE DIST BRACKETS

**SPOOLS** -

- 0 - NONE
- 1 - 4 SPOOLS
- 2 - 8 SPOOLS

**MATRIX ENCLOSURE ORDER EXAMPLE:**

DCXS	1	1	3	3	1	2	2	2	2
SERIES	CBL FLOW	COLOR	TOP PANEL	BOTTOM PANEL	DOORS	SIDE PANEL	REAR PANEL	HSG CBL ATTACHMENT	SPOOLS

**MATRIX DESCRIPTION**

84.00h x 36w x 15d DCXS SERIES ENCLOSURE  
LEFT TO RIGHT FLOW  
CENTRAL OFFICE WHITE w/  
TOP BRUSH + (8) CABLE BRACKETS,  
BOT BRUSH + (8) CABLE BRACKETS,  
BI-FOLD PLEXIGLASS DOOR,  
SOLID SIDE PANEL  
CABLE MANAGEMENT REAR PANEL  
8 BRACKET (96 CABLE) / 16 LPM BRACKETS  
8 SPOOLS

\*BY DEFAULT TOP, BOTTOM, SIDE, REAR PANELS AND CABLE  
MANAGEMENT ACCESSORIES ARE POWDER COATED TO MATCH  
FRAME COLOR

\*\*BY DEFAULT DOORS ARE POWDER COATED BLACK MEDIUM  
TEXTURE

STANDARD WHITE ENCLOSURES WILL HAVE BLACK DOORS /  
STANDARD BLACK ENCLOSURES WILL HAVE BLACK DOORS

CONSULT FACTORY FOR SPECIAL COLOR OPTIONS AND/OR  
ENCLOSURE CONFIGURATIONS

THIS DRAWING AND ALL INFORMATION CONTAINED HEREIN IS THE PROPERTY OF BELDEN. ANY USE, COPY OR REPRODUCTION OF THIS MATERIAL WITHOUT WRITTEN PERMISSION OF BELDEN IS PROHIBITED			
DCXS SERIES MASTER			
DCXS SERIES - MATRIX ORDERING			
APPROVED BY: RCG			
APPROVAL DATE: 9/13/19			
UNITS : INCH	SH 1 of 4	C	SUBMITTAL
SCALE: 3:32	DATE: 9/13/2019		