



DCX FRAME DETAILS

- WELDED 14GA FORMED STEEL CONSTRUCTION
- ALL FRAMES SEISMICALLY RATED TO AC156 AND GR63 (CERTIFICATIONS AVAILABLE UPON REQUEST)
- RIGHT-TO-LEFT OR LEFT-TO-RIGHT CABLE FLOW DIRECTIONS
- ROOM FOR (8) 4U HOUSINGS
- EACH ENCLOSURE IS IDENTIFIED/TRACKED BY A UNIQUE SERIAL NUMBER
- ALL REMOVABLE DOORS ARE GROUNDED TO FRAME BY USE OF BONDING STRAPS AND/OR BONDING HARDWARE
- ALL ENCLOSURES INCLUDE LEVERS
LEVERS MUST BE REMOVED FOR SEISMIC APPLICATIONS





UNIQUE SERIAL NUMBER
LOCATED ON BOTTOM
FRONT SILL OF EACH ENCLOSURE


DETAIL A
SCALE 3/8



LEFT TO RIGHT
FEED FRAME SHOWN




GROUND SYMBOL



1/4-20 x 3/4
GROUNDING STUD
(3) PLACES AT THE BASE
OF EACH POST


DETAIL B
SCALE 3/8

GROUND SYMBOL



1/4-20 x 3/4
GROUNDING STUD
(2) PLACES AT THE TOP
OF OUTER BASE POST

DETAIL C
SCALE 3:8



BELDEN

THIS DRAWING AND ALL INFORMATION CONTAINED HEREIN IS THE PROPERTY OF BELDEN. ANY USE, COPY OR REPRODUCTION OF THIS MATERIAL WITHOUT WRITTEN PERMISSION OF BELDEN IS PROHIBITED

DCXS SERIES MASTER

DCXS SERIES - FRAME DETAILS

APPROVED BY: RCG

APPROVAL DATE: 9/13/19

UNITS: INCH

SH 2 of 4

C

SCALE: 3:32

DATE: 9/13/2019

SUBMITTAL