

CABLE-PWR-SAFD-SAFD



TYPE	PARAMETER	SPECIFICATION	NOTES
Connectors	Plug	SAF-D-GRID® 300 VOLT (3-6074P10), KEY A	Registered trademark of Anderson Power
	Connector	SAF-D-GRID® 300 VOLT (3-6074P10), KEY A	
Electrical	Current Rating	20A	
	Length	6.60 ft (2.00m)	
	Wire Gauge	12AWG	
Mechanical	Jacket Type	SJT	
	Temperature rating	90°C (°F)	
Environment Approvals	Safety	cURus TO UL 1977, FILE# E26226	
	Environmental	RoHS, REACH	

CABLE-PWR-SAFD-C20P



TYPE	PARAMETER	SPECIFICATION	NOTES
Connectors	Plug	IEC 320-C20	Registered trademark of Anderson Power
	Connector	SAF-D-GRID® 300 VOLT (3-6074P10), KEY A	
Electrical	Current Rating	20A	
	Length	6.60 ft (2.00m)	
	Wire Gauge	12AWG	
Mechanical	Jacket Type	SJT	
	Temperature rating	90°C (°F)	
Environment Approvals	Safety	cURus TO UL 1977, FILE# E26226	
	Environmental	RoHS, REACH	

CABLE-PWR-SAFD-L620P



TYPE	PARAMETER	SPECIFICATION	NOTES
Connectors	Plug	L6-20P	Registered trademark of Anderson Power
	Connector	SAF-D-GRID® 300 VOLT (3-6074P10), KEY A	
Electrical	Current Rating	20A	
	Length	6.60 ft (2.00m)	
	Wire Gauge	12AWG	
Mechanical	Jacket Type	SJT	
	Temperature rating	90°C (°F)	
Environment Approvals	Safety	cURus TO UL 1977, FILE# E26226	
	Environmental	RoHS, REACH	

CABLE-PWR-SAFD-L720P



TYPE	PARAMETER	SPECIFICATION	NOTES
Connectors	Plug	L7-20P	Registered trademark of Anderson Power
	Connector	SAF-D-GRID® 300 VOLT (3-6074P10), KEY A	
Electrical	Current Rating	20A	
	Length	6.60 ft (2.00m)	
	Wire Gauge	12AWG	
Mechanical	Jacket Type	SJT	
	Temperature rating	90°C (°F)	
Environment Approvals	Safety	cURus TO UL 1977, FILE# E26226	
	Environmental	RoHS, REACH	