

# 无线电发射设备型号核准证

Radio Transmission Equipment Type Approval Certificate

附页一

Attachment 1

设备型号(Equipment Type): DAP849

核准代码(CMIIT ID): 25J99578T663

技术体制/射频模块 Technical Scheme/ RF Module	工作频率范围 Operating Frequency Range	调制方式 Modulation Mode	频率容限 Frequency Tolerance	占用带宽 Occupied Bandwidth	发射功率限值 Transmitting Power Limits	杂散发射限值 Spurious Emission Limits
无线局域网	5725-5850MHz 5150-5350MHz 2400-2483.5MHz	BPSK/QPSK/16QAM/64QAM/256QAM/1024QAM/DBP SK/DQPSK/CCK	$\leq 20$ ppm	$\leq 80$ MHz $\leq 80$ MHz $\leq 40$ MHz	$\leq 33$ dBm (e. i. r. p.) $\leq 23$ dBm (e. i. r. p.) $\leq 20$ dBm (e. i. r. p.)	$\leq -30$ dBm

备注 (Notes):

具体杂散发射限值符合工信部无【2021】129号要求。

审核机构

Sealed by Approving Agency

2025年10月24日

Year Month Date