

Belden PDU Specification

Part #: 9BB2-081002

Description:

Basic, Standard, 30A, 208V, Horizontal/Vertical, (8) IEC C13, breakerred, 10 ft power cord with L6-30P, Black Powder Coat.



Specification:

Quantity Of Inputs	1
Voltage	208V
Current	30A
VA per Input (Load Capacity)	4.9kW
Frequency	50/60 Hz
Over Current Protection	(4) 15A Thermal Breakers
Switch	No
Power Cable Wire Gauge	10/3
Power Cable Length	10ft
Plug Type	NEMA L6-30P Twistlock
Receptacle/Socket Type #1	IEC C13
- Quantity on Face	8
- Quantity per Breaker Pair	4
- Style	Banks of 4
- Maximum Output per Receptacle/Socket	15A per receptacle bank

Belden PDU Specification



Part #: 9BB2-081002

- Voltage per Receptacle/Socket	208V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	17 in / 432 mm Vertical/Horizontal Rackmount
19in Panel Mount Brackets	Yes
SLB-4 Brackets	Yes
Made in the USA	Yes
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed Accessory 1950
Chassis Dimensions (LxWxD)	17.00in x 1.72in x 1.61in
Shipped Weight	6lbs (2.72kg)

To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____