

# Belden PDU Specification

**Part #: 9LG2-101004**

**Description:**

Basic, 20A, 120V, Horizontal, (10) NEMA 5-20R, power switch, breakered, 10 ft power cord with L5-20P, Current - Local

Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input. Black Powder Coat.



**Specification:**

Monitoring	Current - Local
1.	Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
2. Monitoring Level 1	Aggregate - Total Unit Monitoring
3. Quantity Of Inputs	1
4. Voltage	120V
5. Current	20A
6. VA per Input (Load	1.9kW

# Belden PDU Specification

**Part #: 9LG2-101004**

	Capacity)	
7.	Frequency	50/60 Hz
8.	Over Current Protection	20A Thermal Breaker
9.	Switch	Yes
10.	Indicators - LED(s)	1 - Power ON Green LED
11.	Power Cable Wire Gauge	12/3
12.	Power Cable Length	10ft
13.	Plug Type	NEMA L5-20P Twistlock
14.	Receptacle/Socket Type #1	NEMA 5-20R
15.	Quantity on Rear #1	10
16.	Quantity per Breaker #1	10
17.	Style #1	Duplex
18.	Maximum Output per Receptacle/Socket #1	20A
19.	Voltage per Receptacle/Socket #1	120V
20.	Continuous Operating Temperature Range	10-45C / 50-113F
21.	Heavy Steel - Powder Coat Finish	Black
22.	Configuration	19in / 435mm Horizontal Rackmount
23.	Flush Mount	Yes
24.	Made in the USA	Yes
25.	Product Warranty	5-year limited warranty
26.	Certification/Agency Approvals	RoHS Compliant

# Belden PDU Specification



**Part #: 9LG2-101004**

---

27.	Certification/Agency Approvals	UL & c-UL Listed 60950
28.	Chassis Dimensions (HxWxD)	1.72in x 17in x 4.50in
29.	Shipped Weight	8lbs (3.63kg)

---

**To insure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.**

Company: \_\_\_\_\_

Authorized  
Customer Signature: \_\_\_\_\_ Date: \_\_\_\_\_