

Belden PDU Specification

Part #: 9BB2-301090

Description:

Basic, Standard, 30A, 208V, Vertical, (24) IEC C13, (6) IEC C19, breakered, 10 ft power cord with L6-30P, Black Powder Coat.



Specification:

1.	Quantity Of Inputs	1
2.	Voltage	208V
3.	Current	30A
4.	VA per Input (Load Capacity)	4.9kW
5.	Frequency	50/60 Hz
6.	Over Current Protection	(2) 20A Double Pole Magnetic Breakers
7.	Switch	Breaker/Switch Combination
8.	Power Cable Wire Gauge	10/3
9.	Power Cable Length	10ft
10.	Plug Type	NEMA L6-30P Twistlock
11.	Combined Total Receptacle/Socket Quantity	30
12.	Receptacle/Socket Type #1	IEC C13
13.	- Quantity on Face	24
14.	- Quantity per Breaker	12
15.	- Style	Banks of 4
16.	- Maximum Output per Receptacle/Socket	15A per receptacle bank
17.	- Voltage per Receptacle/Socket	208V
18.	Receptacle/Socket Type #2	IEC C19
19.	- Quantity on Face	6
20.	- Quantity per Breaker	3
21.	- Style	Individual
22.	- Maximum Output per Receptacle/Socket	20A
23.	- Voltage per Receptacle/Socket	208V

Belden PDU Specification



Part #: 9BB2-301090

24.	Continuous Operating Temperature Range	10-45C / 50-113F
25.	Heavy Steel - Powder Coat Finish	Black
26.	Configuration	66 in / 1683 mm Vertical Rackmount
27.	7938 Vertical Mounting Bracket Kit	Yes
28.	Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
29.	Made in the USA	Yes
30.	Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
31.	Certification/Agency Approvals	RoHS Compliant
32.	Certification/Agency Approvals	UL & c-UL Listed 60950
33.	Chassis Dimensions (LxWxD)	66.25in x 2.0in x 2.0in
34.	Doghouse (D)	1.44in
35.	Shipped Weight	17lbs (7.71kg)

To ensure customer satisfaction with this product, prior to acceptance of an order, Belden requires a signature of approval for the specification above.

Company: _____

Authorized
Customer Signature: _____ Date: _____