


DOORS

- ENCLOSURE DEFAULT IS A LOCKING SWING HANDLE, KEYED CH751
- * CUSTOM KEYED HANDLE AVAILABLE ON REQUEST
- * CONSULT I.S. CATALOG FOR SMART ACCESS OPTIONS

- ALL SINGLE DOORS COME STANDARD w/ SINGLE POINT LATCHING
- * 3PT LATCHING AVAILABLE ON REQUEST

- ALL SPLIT DOORS COME STANDARD w/ 3PT LATCHES

- CONSTRUCTION OF PERFORATED DOORS CONSISTS OF WELDED 16GA CRS CROSS MEMBERS w/ 18GA SQUARE TUBING STIFFENERS AND SINGLE 18GA CRS SHEET METAL PUNCHED w/ HEXAGONAL OPENINGS.
- CONSTRUCTION OF SOLID DOORS CONSISTS OF WELDED 18GA SQUARE TUBING STIFFENERS AND 18GA CRS SHEET METAL.
- ALL VIEWS SHOW DOORS FROM INSIDE
- ALL DOORS ADD DEPTH TO THE FRAME DIMENSION (SEE LIST BELOW EACH DOOR)




CURVED PERFORATED
SCALE 3/32
ADDS ~2.60 IN TO CABINET DEPTH PER DOOR

FLAT PERFORATED
SCALE 3/32
ADDS 1.250 IN TO CABINET DEPTH PER DOOR


SPLIT PERFORATED
SCALE 3/32
ADDS 1.125 IN TO CABINET DEPTH PER DOOR

FLAT SOLID
SCALE 3/32
ADDS 1.250 IN TO CABINET DEPTH PER DOOR ¹

SPLIT SOLID
SCALE 3/32
ADDS 0.980 IN TO CABINET DEPTH PER DOOR



2	CORRECTED SPLIT DOOR WIDTH (WAS 1.050)	RCG	4/25/17
1	CORRECTED FLAT SOLID DOOR THK (WAS .980)	RCG	11/3/16



BELDEN

THIS DRAWING AND ALL INFORMATION CONTAINED HEREIN IS THE PROPERTY OF BELDEN. ANY USE, COPY OR REPRODUCTION OF THIS MATERIAL WITHOUT WRITTEN PERMISSION OF BELDEN IS PROHIBITED

XHM SERIES MASTER - DOOR OPTIONS

HYBRID XHM SERIES - DOOR DETAILS




APPROVED BY:	RCG
APPROVAL DATE:	9/29/16
UNITS:	INCH
SCALE:	3:32
SH	5 of 8
DATE:	9/29/2016

SUBMITTAL


DOORS (CONTINUED)

- ENCLOSURE DEFAULT IS A LOCKING SWING HANDLE, KEYED CH751
- * CUSTOM KEYED HANDLE AVAILABLE ON REQUEST
- * CONSULT I.S. CATALOG FOR SMART ACCESS OPTIONS
- ALL SINGLE DOORS COME STANDARD w/ SINGLE POINT LATCHING
- * 3PT LATCHING AVAILABLE ON REQUEST
- ALL SPLIT DOORS COME STANDARD w/ 3PT LATCHES

- CONSTRUCTION OF PERFORATED DOORS CONSISTS OF WELDED 16GA CRS CROSS MEMBERS w/ 18GA SQUARE TUBING STIFFENERS AND SINGLE 18GA CRS SHEET METAL PUNCHED w/ HEXAGONAL OPENINGS.
- CONSTRUCTION OF SOLID DOORS CONSISTS OF WELDED 18GA SQUARE TUBING STIFFENERS AND 18GA CRS SHEET METAL.
- ALL VIEWS SHOW DOORS FROM OUTSIDE
- ALL DOORS ADD DEPTH TO THE FRAME DIMENSION (SEE LIST BELOW EACH DOOR)



VENTED w/ POLY WINDOW
SCALE 3/32
ADDS 1.375 IN TO CABINET
DEPTH PER DOOR



SOLID w/ POLY WINDOW
SCALE 3/32
ADDS 1.375 IN TO CABINET
DEPTH PER DOOR

BELDEN			
<small>THIS DRAWING AND ALL INFORMATION CONTAINED HEREIN IS THE PROPERTY OF BELDEN. ANY USE, COPY OR REPRODUCTION OF THIS MATERIAL WITHOUT WRITTEN PERMISSION OF BELDEN IS PROHIBITED</small>			
XHM SERIES MASTER - DOOR OPTIONS			
HYBRID XHM SERIES - DOOR DETAILS			
APPROVED BY: RCG			
APPROVAL DATE: 1/2/19			
UNITS: INCH	SH 5a of 8	C	SUBMITTAL
SCALE: 3:32	DATE: 1/2/2019		

