

Weight:	450 g
Ambient Temperature (Operation):	-20 °C to 70 °C
Ambient Temperature (Storage/Transport):	-25 °C to 85 °C
Permissible Humidity (Operation):	5 % ... 95 % (For UL applications max. 80 %)
Permissible Humidity (Storage/Transport):	5 % ... 95 % (For UL applications max. 80 %)
Air Pressure (Operation):	80 kPa ... 106 kPa (up to 2000 m above sea level)
Air Pressure (Storage/Transport):	80 kPa ... 106 kPa (up to 2000 m above sea level)
Flammability Class:	UL 94 (IEC 61010)
Protection Class:	III, IEC 61140, EN 61140, VDE 0140-1
Pollution Degree:	3 acc. to EN 60664-1, VDE 0110-1
Vibration Resistance:	15 g / 5 -500 Hz
Shock Resistance:	50 g / 11ms
Mean Time To Failure (MTTF):	612 years. acc. to Telcordia SR-332 (2011) 20°C
Contact Base Material:	M12 Hybrid, Y-coded, CuSn, Gold-plated
Contact Bearer Material:	PA
O-Ring Material:	FKM
Mounting:	2 hole screw mounting. Use standard M4 x 25 / 30 screws with toothed lock washer (as per DIN 125) and self-locking nuts.
Fastening Torque (Fixing Screw):	M4: 1 Nm
Fastening Torque (Ground Connection (FE)):	M4: 1 Nm
Fastening Torque (Bus Connection):	M12: 0.5 Nm
Fastening Torque (Power Connection):	M12: 0.5 Nm
Fastening Torque (I/O Connection):	M12: 0.5 Nm
Included in Delivery:	Attachable Labels: 15x, Sealing Caps: 5x M12

PROFINET

Protocol:	PROFINET
Connection:	M12 Hybrid, 8-poles, Y-coded
Number of Connections:	2
Specification:	V2.3X
Conformance Class:	C
Performance Class:	RT (switch supports IRT)
Netload Class:	II
Transmission Rate:	Fast Ethernet (10/100 Mbit/s), Full Duplex
Transmission Method:	100 BASE-TX, with auto negotiation and auto crossing
Cycle Time / Update Rate:	min. 1 ms
Addressing:	DCP
Fast Startup (FSU):	Supported, ≤ 2000 ms
Media Redundancy Protocol (MRP):	Supported, MRP client
Shared Device:	Supported
Topology Detection:	LLDP, SNMP V1
Easy Device Replacement:	Supported, based on LLDP
Supported Network Protocols (Other):	ARP, HTTP, Ping, SNMP V1, TCP/IP

EtherNet/IP

Protocol:	EtherNet/IP
Connection:	M12 Hybrid, 8-poles, Y-coded
Number of Connections:	2
Specification:	CIP V3.1x, EIP Adaption of CIP V1.1x
Transmission Rate:	Fast Ethernet (10/100 Mbit/s), Full Duplex
Transmission Method:	100 BASE-TX, with auto negotiation and auto crossing
Cycle Time / Requested Packet Interval (RPI):	min. 1 ms
Addressing:	BootP, DHCP, Rotary Address Switches
Address Switches Range:	0 to 255 dec
Connection Types:	Exclusive Owner, Input Only, Listen Only
CIP Msg Connection Limit:	6
CIP I/O Connection Limit:	3
Device Level Ring (DLR):	Supported, beacon based

Quick Connect (QC):	Not supported
Supported Network Protocols (Other):	ACD, ARP, BootP, DHCP, HTTP, IGMP, Ping, TCP/IP

Power Supply

Connection Module Supply Voltage:	M12 Hybrid, 8-poles, Y-coded
Number of Connections:	2
Current Carrying Capacity of Connector:	max. 6 A
Module Supply Voltage (Nominal):	24 V DC (SELV/PELV)
Module Supply Voltage (Range):	18 V DC to 30 V DC
Current Consumption (typ.):	180 mA (at 24 V DC)
Reverse Polarity Protection:	Yes
Status Indicator:	LED green
Diagnostic Indicator:	LED red
Connection Sensor Supply Voltage:	M12 Power, 5-poles, L-coded
Current Carrying Capacity of Connector:	max. 6 A
Sensor Supply Voltage (Nominal):	24 V DC (SELV/PELV)
Sensor Supply Voltage (Range):	18 V DC to 30 V DC
Reverse Polarity Protection:	Yes
Status Indicator:	LED green
Diagnostic Indicator:	LED red
Connection Actuator Supply Voltage:	via Module Supply Connection
Current Carrying Capacity of Connector:	max. 6 A
Actuator Supply Voltage (Nominal):	24 V DC (SELV/PELV)
Actuator Supply Voltage (Range):	18 V DC to 30 V DC
Reverse Polarity Protection:	Yes
Status Indicator:	LED green
Diagnostic Indicator:	LED red

IO-Link Master Channels

Number of IO-Link Master Channels:	max. 8, configurable
Connection:	M12, 5-poles, A-coded
IO-Link Class A Ports:	4x, X1 to X4
IO-Link Class B Ports:	4x, X5 to X8
IO-Link Specification:	V1.1.2
Parameter Storage:	Supported
Supported COM Modes:	4.8 kBaud (COM 1), 38.4 kBaud (COM 2), 230.4 kBaud (COM 3)
Cycle Time / Update Rate:	min. 8 ms for all channels at 32 Byte IN / OUT
Nominal Voltage:	24 V DC via US (system power supply)
Nominal Current C/Q (Pin 4):	max. 500 mA (via US)
Nominal Current 1L+ (Pin 1):	max. 500 mA (via US)
Nominal Current 2L+/Uaux (Pin 2, B Ports):	max. 4 A per module (via Uaux)
Perm. Conductor Length to Device:	≤ 20 m
Status Indicator:	LED green per channel
Diagnostic Indicator:	LED red per port

Digital Input Channels

Number of Digital Input Channels:	max. 12, configurable
Connection:	M8, 5-poles, B-coded
Number of Ports:	8x, X1 to X8
Channel Type:	Type 1 acc. to IEC 61131-2
Input Wiring:	2-, 3-wire
Nominal Voltage:	24 V DC via US (module power supply)
Nominal Current:	typ. 3 mA
Sensor Current Supply:	max. 500 mA per port via 1L+
Sensor Type:	PNP
Input Voltage Range "0" signal:	-0,3V DC ... 5 V DC
Input Voltage Range "1" signal:	15 V DC ... 30 V DC

Protective Circuit:	Electronically: Overload protection, short-circuit protection
Status Indicator:	LED white or yellow per channel
Diagnostic Indicator:	LED red per port

Digital Output Channels

Number of Digital Output Channels:	max. 8, configurable
Connection:	M8, 5-poles, B-coded
Number of Ports:	8x, X1 to X8
Channel Type:	p-switching
Output Wiring:	2-wire
Nominal Voltage:	24 V DC via US (system power supply)
Output Current per Channel:	max. 0.5 A (Pin 4)
Output Current per Module:	max. 6 A
Galvanically Isolated:	No
Protective Circuit:	Electronically: Overload protection, short-circuit protection
Overload Behavior:	Auto off and on switching / Manual restart
Status Indicator:	LED white or yellow per channel
Diagnostic Indicator:	LED red per port

Electrical Isolation

US (System Supply Voltage) / FE:	500 V DC
Uaux / FE:	500 V DC
Bus connection / FE:	2000 V DC

EMC Conformance

EMC Directive:	2014/30/EU
EN 61000-4-2 Electrostatic Discharge (ESD):	Criterion B; 4 kV contact discharge, 8 kV air discharge
EN 61000-4-3 Electromagnetic Field:	Criterion A; Field intensity: 10 V/m
EN 61000-4-4 Fast Transients (Burst):	Criterion B, 2 kV
EN 61000-4-5 Surge Voltage:	Criterion B; DC supply lines: ± 0.5 kV/ ± 0.5 kV (symmetrical/asymmetrical); For I/O ports with cables ≤ 30 m
EN 61000-4-6 Conducted immunity:	Criterion A; Test voltage 10 V
EN 55022 Radio Interference Properties:	Class A

Safety & Environmental Compliance

CE:	Yes
RoHS Compliant:	Yes
China RoHS-Compliant:	Yes

Approvals

UL:	cULus Listed, UL 61010-1
UL-File:	E230848
CSA:	Yes, via UL
IO-Link:	Yes

Notes

Protection Degree / IP Rating Note:	*only if mounted and locked in combination with Hirschmann / Lumberg Automation connector.
System Power Supply Connection Note:	*do not connect / disconnect under voltage!
Update and Revision:	Revision Number: 0.27 Revision Date: 08-29-2019

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.