



Product: [10GX UTP CMP PATCH CORDS](#)

10GX UTP CMP Patch Cords

Product Description

10GX UTP CMP Patch Cords

Technical Specifications

Product Overview

Suitable Applications:	IBDN System 10GX, TIA Category 6A, ISO Class EA, 10GBASE-T
------------------------	--

Physical Characteristics (Overall)

Total Number of Pairs:	4
Overall Nominal Diameter:	0.255 in
Wiring Scheme:	T568A/B-T568A/B
Packaging:	Individually packaged in a clear plastic bag.

Connectors

Materials

Description	Material	Color
Boot	Elastomer	Translucent
Conductor	BC - Bare Copper	
Front Connection	Blades Phosphor Bronze with 50u inch Gold over Nickel Plating	
Inner Jacket	PVC - Polyvinyl Chloride	
Insulation	PO - Polyolefin	
Outer Jacket	PVC - Polyvinyl Chloride	

Electrical Characteristics

Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute
Current Rating:	1.500 A
Insulation Resistance:	500 M-Ohm Minimum
Max Contact Resistance:	20 mOhm

Temperature Range

Installation Temp Range:	-10°C To +60°C
Storage Temp Range:	-40°C To +70°C
Operating Temp Range:	-10°C To +60°C

Mechanical Characteristics

Min Bend Radius (Overall Cable):	1.040 in
Plug /Jack Compatibility:	RJ45

Termination Interface

Connection	Durabilities
Mated Connection	750 Cycles

Standards

UL Rating:	Plenum
Data Category:	Category 6A
TIA/EIA Compliance:	Category 6A - TIA 568-C.2, Class EA - ISO/IEC 11801:2002 Ed.2 Amendment 2
Other Compliance:	FCC Part 68, Subpart F, IEC 60603-7

Applicable Environmental and Other Programs

Environmental Space:	Plenum
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2006-01-01
MII Order #39 (China RoHS):	EUP 50

Flammability, LS0H, Toxicity Testing

Safety Listing:	c(UL)us Listed
-----------------	----------------

Part Number

Related Parts:	10GX Modular Jacks and Couplers, 10GX Patch Panels
----------------	--

Variants

Item #	Color	Length
CA22100048	Black	48 ft
CA22100050	Black	50 ft
CA22100060	Black	60 ft
CA22100150	Black	150 ft
CA22106001	Blue	1 ft
CA22106003	Blue	3 ft
CA22106004	Blue	4 ft
CA22106006	Blue	6 ft
CA22106007	Blue	7 ft
CA22106010	Blue	10 ft
CA22106015	Blue	15 ft
CA22106050	Blue	50 ft
CA22106060	Blue	60 ft
CA22106125	Blue	125 ft
CA22106250	Blue	250 ft
CA22103004	Orange	4 ft
CA22103007	Orange	7 ft
CA22103010	Orange	10 ft
CA22103015	Orange	15 ft
CA22103017	Orange	17 ft
CA22103050	Orange	50 ft
CA22109002	White	2 ft
CA22109006	White	6 ft
CA22109007	White	7 ft
CA22109010	White	10 ft
CA22109015	White	15 ft
CA22109020	White	20 ft
CA22109025	White	25 ft
CA22109030	White	30 ft
CA22109033	White	33 ft
CA22109035	White	35 ft
CA22109050	White	50 ft
CA22109066	White	66 ft
CA22109200	White	200 ft
CA22104001	Yellow	1 ft
CA22104010	Yellow	10 ft
CA22104015	Yellow	15 ft

Product Notes

Labeling:	Belden Part Number, Performance Acronym, Wiring Scheme and Cord Length
-----------	--

History

Update and Revision:	Revision Number: 0.162 Revision Date: 01-31-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.