



Product: [10GX UTP CMR TRACEABLE CORDS](#) 

10GX UTP CMR Traceable Cords

Product Description

10GX UTP CMR Traceable Cords

Technical Specifications

Product Overview

| | |
|------------------------|--|
| Suitable Applications: | IBDN System 10GX, TIA Category 6A, ISO Class EA, 10GBASE-T. 20 and 40 sec. flashing high intensity LED Battery operated (included), push button activated. |
|------------------------|--|

Physical Characteristics (Overall)

| | |
|---------------------------|---|
| Total Number of Pairs: | 4 |
| Overall Nominal Diameter: | 0.265 in |
| Wiring Scheme: | T568A/B-T568A/B |
| Packaging: | Individually packaged in a clear plastic bag. |

Connectors

Materials

| Description | Material | Color |
|------------------|---|-------------|
| Boot | Elastomer | Translucent |
| Conductor | BC - Bare Copper | |
| Front Connection | Blades Phosphor Bronze with Tin Plating over Nickel | |
| Inner Jacket | PVC - Polyvinyl Chloride | |
| Insulation | PO - Polyolefin | |
| Outer Jacket | PVC - Polyvinyl Chloride | |

Electrical Characteristics

| | |
|-------------------------|----------------------------------|
| Dielectric Strength: | 1,000 V RMS @ 60 Hz for 1 minute |
| Current Rating: | 1.500 A |
| Insulation Resistance: | 500 M-Ohm Minimum |
| Max Contact Resistance: | 20 mOhm |

Temperature Range

| | |
|--------------------------|----------------|
| Installation Temp Range: | -10°C To +60°C |
| Storage Temp Range: | -40°C To +70°C |
| Operating Temp Range: | -10°C To +60°C |

Mechanical Characteristics

| | |
|----------------------------------|----------|
| Min Bend Radius (Overall Cable): | 1.040 in |
| Plug /Jack Compatibility: | RJ45 |

Termination Interface

| Connection | Durabilities |
|------------------|--------------|
| Mated Connection | 750 Cycles |

Standards

| | |
|---------------------|---|
| UL Rating: | Riser |
| Data Category: | Category 6A |
| TIA/EIA Compliance: | Category 6A - TIA 568-C.2, Class EA - ISO/IEC 11801:2002 Ed.2 Amendment 2 |
| Other Compliance: | FCC Part 68, Subpart F, IEC 60603-7 |

Applicable Environmental and Other Programs

| | |
|---------------------------------------|------------|
| Environmental Space: | Riser |
| EU Directive 2002/95/EC (RoHS): | Yes |
| EU RoHS Compliance Date (yyyy-mm-dd): | 2006-01-01 |
| MII Order #39 (China RoHS): | EUP 50 |

Flammability, LS0H, Toxicity Testing

| | |
|-----------------|----------------|
| Safety Listing: | c(UL)us Listed |
|-----------------|----------------|

Part Number

| | |
|----------------|--|
| Related Parts: | 10GX Modular Jacks and Couplers, 10GX Patch Panels |
|----------------|--|

Variants

| Item # | Color | Length |
|------------|-------|--------|
| CAT1100001 | Black | 1 ft |
| CAT1100002 | Black | 2 ft |
| CAT1100003 | Black | 3 ft |
| CAT1100004 | Black | 4 ft |
| CAT1100005 | Black | 5 ft |
| CAT1100006 | Black | 6 ft |
| CAT1100007 | Black | 7 ft |
| CAT1100008 | Black | 8 ft |
| CAT1100009 | Black | 9 ft |
| CAT1100010 | Black | 10 ft |
| CAT1100011 | Black | 11 ft |
| CAT1100012 | Black | 12 ft |
| CAT1100013 | Black | 13 ft |
| CAT1100014 | Black | 14 ft |
| CAT1100015 | Black | 15 ft |
| CAT1100020 | Black | 20 ft |
| CAT1100025 | Black | 25 ft |
| CAT1106001 | Blue | 1 ft |
| CAT1106002 | Blue | 2 ft |
| CAT1106003 | Blue | 3 ft |
| CAT1106004 | Blue | 4 ft |
| CAT1106005 | Blue | 5 ft |
| CAT1106006 | Blue | 6 ft |
| CAT1106008 | Blue | 8 ft |
| CAT1106009 | Blue | 9 ft |
| CAT1106010 | Blue | 10 ft |
| CAT1106011 | Blue | 11 ft |
| CAT1106012 | Blue | 12 ft |
| CAT1106013 | Blue | 13 ft |
| CAT1106014 | Blue | 14 ft |
| CAT1106015 | Blue | 15 ft |
| CAT1106020 | Blue | 20 ft |
| CAT1106025 | Blue | 25 ft |
| CAT1106030 | Blue | 30 ft |
| CAT1106035 | Blue | 35 ft |
| CAT1106050 | Blue | 50 ft |
| CAT1106080 | Blue | 80 ft |
| CAT1106100 | Blue | 100 ft |
| CAT1108001 | Gray | 1 ft |
| CAT1108002 | Gray | 2 ft |

| | | |
|------------|--------|--------|
| CAT1108003 | Gray | 3 ft |
| CAT1108005 | Gray | 5 ft |
| CAT1108006 | Gray | 6 ft |
| CAT1108007 | Gray | 7 ft |
| CAT1108008 | Gray | 8 ft |
| CAT1108009 | Gray | 9 ft |
| CAT1108010 | Gray | 10 ft |
| CAT1108011 | Gray | 11 ft |
| CAT1108012 | Gray | 12 ft |
| CAT1108013 | Gray | 13 ft |
| CAT1108014 | Gray | 14 ft |
| CAT1108020 | Gray | 20 ft |
| CAT1108025 | Gray | 25 ft |
| CAT1105001 | Green | 1 ft |
| CAT1105002 | Green | 2 ft |
| CAT1105003 | Green | 3 ft |
| CAT1105004 | Green | 4 ft |
| CAT1105005 | Green | 5 ft |
| CAT1105006 | Green | 6 ft |
| CAT1105007 | Green | 7 ft |
| CAT1105008 | Green | 8 ft |
| CAT1105009 | Green | 9 ft |
| CAT1105010 | Green | 10 ft |
| CAT1105011 | Green | 11 ft |
| CAT1105012 | Green | 12 ft |
| CAT1105013 | Green | 13 ft |
| CAT1105014 | Green | 14 ft |
| CAT1105015 | Green | 15 ft |
| CAT1105020 | Green | 20 ft |
| CAT1105025 | Green | 25 ft |
| CAT1105050 | Green | 50 ft |
| CAT1105100 | Green | 100 ft |
| CAT1103001 | Orange | 1 ft |
| CAT1103002 | Orange | 2 ft |
| CAT1103003 | Orange | 3 ft |
| CAT1103004 | Orange | 4 ft |
| CAT1103005 | Orange | 5 ft |
| CAT1103006 | Orange | 6 ft |
| CAT1103007 | Orange | 7 ft |
| CAT1103008 | Orange | 8 ft |
| CAT1103009 | Orange | 9 ft |
| CAT1103010 | Orange | 10 ft |
| CAT1103011 | Orange | 11 ft |
| CAT1103012 | Orange | 12 ft |
| CAT1103013 | Orange | 13 ft |
| CAT1103014 | Orange | 14 ft |
| CAT1103015 | Orange | 15 ft |
| CAT1103020 | Orange | 20 ft |
| CAT1103025 | Orange | 25 ft |
| CAT1102001 | Red | 1 ft |
| CAT1102002 | Red | 2 ft |
| CAT1102003 | Red | 3 ft |
| CAT1102004 | Red | 4 ft |
| CAT1102005 | Red | 5 ft |
| CAT1102006 | Red | 6 ft |
| CAT1102007 | Red | 7 ft |
| CAT1102008 | Red | 8 ft |
| CAT1102009 | Red | 9 ft |
| CAT1102010 | Red | 10 ft |
| CAT1102011 | Red | 11 ft |
| CAT1102012 | Red | 12 ft |

| | | |
|------------|--------|-------|
| CAT1102013 | Red | 13 ft |
| CAT1102014 | Red | 14 ft |
| CAT1102015 | Red | 15 ft |
| CAT1102020 | Red | 20 ft |
| CAT1102025 | Red | 25 ft |
| CAT1109001 | White | 1 ft |
| CAT1109002 | White | 2 ft |
| CAT1109003 | White | 3 ft |
| CAT1109005 | White | 5 ft |
| CAT1109006 | White | 6 ft |
| CAT1109007 | White | 7 ft |
| CAT1109008 | White | 8 ft |
| CAT1109009 | White | 9 ft |
| CAT1109011 | White | 11 ft |
| CAT1109012 | White | 12 ft |
| CAT1109013 | White | 13 ft |
| CAT1109014 | White | 14 ft |
| CAT1109015 | White | 15 ft |
| CAT1109020 | White | 20 ft |
| CAT1109025 | White | 25 ft |
| CAT1109050 | White | 50 ft |
| CAT1104001 | Yellow | 1 ft |
| CAT1104002 | Yellow | 2 ft |
| CAT1104003 | Yellow | 3 ft |
| CAT1104004 | Yellow | 4 ft |
| CAT1104005 | Yellow | 5 ft |
| CAT1104006 | Yellow | 6 ft |
| CAT1104007 | Yellow | 7 ft |
| CAT1104008 | Yellow | 8 ft |
| CAT1104009 | Yellow | 9 ft |
| CAT1104010 | Yellow | 10 ft |
| CAT1104011 | Yellow | 11 ft |
| CAT1104012 | Yellow | 12 ft |
| CAT1104013 | Yellow | 13 ft |
| CAT1104014 | Yellow | 14 ft |
| CAT1104015 | Yellow | 15 ft |
| CAT1104020 | Yellow | 20 ft |
| CAT1104025 | Yellow | 25 ft |

Product Notes

| | |
|-----------|---|
| Labeling: | Belden Part Number, Performance Acronym, Wiring Scheme and Cord Length. |
|-----------|---|

History

| | |
|----------------------|--|
| Update and Revision: | Revision Number: 0.157 Revision Date: 01-31-2020 |
|----------------------|--|

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.