



Product: [10GX REVConnect Panel 24P](#)

10GX REVConnect Patch Panel 24 Port



Product Description

10GX REVConnect Patch Panel, 24-Port, 1U (Preloaded)

Technical Specifications

Product Overview

Suitable Applications:	10GX Systems, TIA Category 6A, ISO Class EA, 10GBASE-T
------------------------	--

Physical Characteristics (Overall)

Height:	1.73 in
Width:	19 in
Depth:	2 in
Port Count:	24 Port
Front Connection:	Flush
Packaging:	Individually packaged in a cardboard box.
Weight:	1.845 lbs

Connectors

Materials

Description	Material	Color
Panel	Steel	Black/White
Frame	PC/ABS	Black/White
Management Bar	Steel	Black
Clear Window	Polycarbonate	Transparent

Construction and Dimensions

Max Capacity:	24 connectors (preloaded)
---------------	---------------------------

Electrical Characteristics

Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute (Signals to Ground)
Current Rating:	1.300 A
Insulation Resistance:	500 M-Ohm Minimum
Termination Resistance:	2.5 mOhm

Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

Mechanical Characteristics

Footprint/Type:	REVConnect
Tool Compatibility:	REVConnect Termination Tool (RVUTT01)

Plug /Jack Compatibility:	RJ45
Cable/Connector Retention:	15 lbs
Connector/Hardware Retention:	20 lbs
Plug/Connector Retention:	11.250 lbs

Standards

UL Rating:	UL94 V-0
Data Category:	Category 6A
TIA/EIA Compliance:	Category 6A - TIA 568.C.2, Category 6A - ISO/IEC 11801:2002 Ed.2
IEEE Compliance:	Power Over Ethernet (PoE) IEEE 802.3at type 1 and 2 (up to 30W), IEEE 802.3bt/D1.7 type 3 and 4 (up to 100W), CISCO UPOE (up to 60W), Power over HDBaseTTM (up to 100W)
Other Standards:	FCC Part 68, Subpart F, IEC 60603-7

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50

Flammability, LSOH, Toxicity Testing

Safety Listing:	c(UL)us Listed
-----------------	----------------

Related Part Numbers

Related Parts:	10GX REVConnect Modular Jacks, 10GX Modular Cords
----------------	---

Variants

Item #	Color	Put-Up Type	UPC
RVAPPF1U24BK	Black	1U	611589225052

Product Notes

Included Parts:	24 10GX REVConnect Jacks Black (RVAMJKUBK-S1); 25 REVConnect Cable Managers and Term; 4 Clear Windows; 1 Rear Cable Management Bar; 4 Screws (10x32); 4 Screws (12x24); 2 Velcro Straps; 4 Frames; 1 Installation Guide
Notes:	For proper installation refer to Installation Guide PX106520 included with the product

History

Update and Revision:	Revision Number: 0.156 Revision Date: 06-02-2023
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.