

**Product:** [1U FAN TRAY A-SERIES](#) 

3U Fan unit with power cord for 19" A-Serie cabinets



## Product Description

Fan unit especially made to fit Belden A-series, free standing cabinets. The unit can be installed horizontally inside the enclosure, fixed to the verticals. Units available with 2, 3 or 4 fans and several plug types.

## Technical Drawing



## Technical Specifications

### Application

Suitable Applications:	Ventilating hot air from a cabinets lower section to the upper section.
Environmental Space:	Indoor

### Construction and Dimensions

Rack Units:	1U
-------------	----

### Mechanical Construction

On-Off Switch:	Yes
Cord Length:	1.9 m

### Environmental and Overall Characteristics

Material:	SPCC cold rolled steel
-----------	------------------------

### Standards

EU CE Mark:	Yes
EU Directive 2011/65/EU (RoHS 2):	Compliant

### Related Part Numbers

Packaging:	Individually packed in a box.
------------	-------------------------------

### Variants

Item #	Number of Fans	Plug Type	Color
--------	----------------	-----------	-------

ADAF2B21	2	BS 1363P	Gray
ADAF2B22	2	BS 1363P	Black
ADAF2B31	3	BS 1363P	Gray
ADAF2B32	3	BS 1363P	Black
ADAF2B41	4	BS 1363P	Gray
ADAF2B42	4	BS 1363P	Black
ADAF2G21	2	16A Schuko	Gray
ADAF2G22	2	16A Schuko	Black
ADAF2G31	3	16A Schuko	Gray
ADAF2G32	3	16A Schuko	Black
ADAF2G41	4	16A Schuko	Gray
ADAF2G42	4	16A Schuko	Black
ADAF2N21	2	5-15P	Gray
ADAF2N22	2	5-15P	Black
ADAF2N31	3	5-15P	Gray
ADAF2N32	3	5-15P	Black
ADAF2N41	4	5-15P	Gray
ADAF2N42	4	5-15P	Black

Update and Revision:	Revision Number: 0.27 Revision Date: 04-08-2022
----------------------	---

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.