




Product: [27254](#) 

MC XLPE/PVC, 2+G C #12+12 Str BC, XLPE Ins E2, AIA Armor, Blk PVC Jkt, 600V MC 90C Dry/Wet SUN RES DIR BUR CT USE

Product Description

UL Type MC (1569) XLPE/PVC, 2+G Conductor 12+12AWG (7x20) Bare Copper, XLPE Insulation E2 Color Code, Aluminum Interlock Armor, Black PVC Outer Jacket, 600V MC 90C Dry/Wet SUN RES DIR BUR CT USE

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
12	7x20	BC - Bare Copper	2
12		BC - Bare Copper	1

Conductor Count:	2
------------------	---

Insulation

Material	Nominal Wall Thickness
XLP, XLPO, XLPE (Thermoset)	0.03 in
No Insulation	

Color Chart

Number	Color
1	Black
2	Red

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.675 in	0.053 in

Construction and Dimensions

Armor

Type of Armor	Material	Diameter over Armoring
Interlocked	Aluminum	0.569 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
1.65 Ohm/1000ft

Current

Max. Recommended Current [A]
20 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
600 V RMS

Temperature Range

UL Temp Rating:	90°C
Operating Temp Range:	-40°C To +90°C
Wet Temp Range:	-40°C To +90 °C
Dry Temp Range:	-40°C To +90 °C

Mechanical Characteristics

Bulk Cable Weight:	192 lbs/1000ft
Max. Pull Tension:	104 lbs
Min Bend Radius/Minor Axis:	7.8 in

Standards

NEC/(UL) Compliance:	MC, XHHW-2
----------------------	------------

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU RoHS Compliance Date (yyyy-mm-dd):	2005-10-13
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 UL Loading
UL voltage rating:	600 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Putup Type	UPC
27254 01010000	Reel	612825328353
27254 0105000	Reel	612825328360
27254 0105000	Reel	612825328360
27254 010S10000	Reel	

History

Update and Revision:	Revision Number: 0.183 Revision Date: 06-24-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.