



**Product:** [37112](#)

Lead Wire, #12 Str TC, EPDM Ins, AWM 3340 AWM 3374

[Request Sample](#)

**Product Description**

Rubber Lead Wire, 12AWG (65x30) Tinned Copper, EPDM Insulation, AWM 3340 AWM 3374 CSA TYPE CL1254 600V 125C FLEX 150C NO FLEX

**Technical Specifications**

**Product Overview**

Suitable Applications:	Class 130(B), 155(F) and also in some 180(H) motor lead systems, high temperature, internal wiring of appliances
------------------------	--

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	No. of Conductors
12	65x30	TC - Tinned Copper	1

Conductor Count:	1
------------------	---

**Insulation**

Material	Nominal Diameter	Nominal Wall Thickness	Min. Average Wall Thickness
EPDM - Ethylene Propylene Diene Monomer	0.19 in	0.052 in	0.045 in

**Electrical Characteristics**

**Voltage**

<b>UL Voltage Rating</b>
600 V RMS

**Temperature Range**

UL Temp Rating:	150°C
-----------------	-------

**Mechanical Characteristics**

Recommended Max Baking Cycles:	24 Hours @ 300°F (149°C) ~ 4 Hours @ 375°F (190°C)
Bulk Cable Weight:	33 lbs/1000ft
Min. Bend Radius/Minor Axis:	0.76 in

**Standards**

UL AWM Style Compliance:	UL AWM Styles 3340, 3374
CSA Rating:	600 V, 125°C
CSA Type:	CL1254

**Applicable Environmental and Other Programs**

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes

EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
CA Prop 65:	Yes
MII Order #39 (China RoHS):	Yes

## Flammability, LSOH, Toxicity Testing

UL voltage rating:	600 V RMS
--------------------	-----------

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	Put-Up Type	Length	UPC
37112 010500	Black	Reel	500 ft	612825146865
37112 0103000	Black	Reel	3,000 ft	612825146858
37112 0105000	Black	Reel	5,000 ft	612825146872
37112 002500	Red	Reel	500 ft	612825146841

Footnote: C - CRATE REEL PUT-UP., F - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'. I - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 200'. M - FINAL PUT-UP LENGTH MAY VARY -10% TO +0% FROM LENGTH SHOWN.

## History

Update and Revision:	Revision Number: 0.358 Revision Date: 08-27-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.