



Product: [4855ANH](#)

12 GHz Coax, 4K UHD Precision Video Coax, RG-59 Mini, 75 Ohm, 23 AWG Solid SC, LSZH Jkt

Product Description

12 GHz Coax, 4K UHD Precision Video Cable, RG-59 Mini, 75 Ohm, 23 AWG solid .023" silver plated copper conductor, gas-injected foam HDPE insulation, Duofoil® bonded to the core + tinned copper braid shield (95% coverage), LSZH jacket.

Technical Specifications

Product Overview

Suitable Applications:	SMPTE 2082-1 12 Gb/s UHD TV, SMPTE 2081-1 6 Gb/s UHD TV, SMPTE 424M 3 Gb/s HD-SDI 1080P
------------------------	---

Construction Details

Conductor

No. of Elements	Size	Stranding	Nom. Diameter	Material
1	23 AWG	Solid	0.023 in	SC - Silvered Copper

Insulation

Material	Nom. Insulation Diameter	Color Code
PE - Polyethylene (Foam)	0.102 in (2.59 mm)	White

Table Notes:	Gas Injected
--------------	--------------

Outer Shield

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
2	Braid	Tinned Copper (TC)		95%

Outer Jacket

Material	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.159 in (4.04 mm)

Overall Cable Diameter (Nominal):	0.159 in (4.04 mm)
-----------------------------------	--------------------

Electrical Characteristics

Return Loss (RL)

Frequency	Min. Return Loss
5 MHz - 1600 MHz	23 dB
1600 MHz - 4500 MHz	21 dB
4500 MHz - 12000 MHz	15 dB

Attenuation

Frequency	Nom. Attenuation
1 MHz	0.39 dB/100ft
3.58 MHz	0.78 dB/100ft
5 MHz	0.92 dB/100ft
6 MHz	1 dB/100ft
7 MHz	1.08 dB/100ft
10 MHz	1.2 dB/100ft

12 MHz	1.3 dB/100ft
25 MHz	1.8 dB/100ft
55 MHz	2.6 dB/100ft
67.5 MHz	2.83 dB/100ft
71.5 MHz	2.93 dB/100ft
88.5 MHz	3.22 dB/100ft
100 MHz	3.39 dB/100ft
135 MHz	3.84 dB/100ft
143 MHz	4.00 dB/100ft
180 MHz	4.41 dB/100ft
270 MHz	5.44 dB/100ft
360 MHz	6.34 dB/100ft
540 MHz	7.85 dB/100ft
720 MHz	9.09 dB/100ft
750 MHz	9.28 dB/100ft
1000 MHz	10.8 dB/100ft
1500 MHz	13.2 dB/100ft
2000 MHz	15.3 dB/100ft
2250 MHz	16.3 dB/100ft
3000 MHz	19.0 dB/100ft
4500 MHz	23.6 dB/100ft
6000 MHz	27.7 dB/100ft
12000 MHz	41.2 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
19.7 Ohm/1000ft (64.6 Ohm/km)	3.9 Ohm/1000ft (13 Ohm/km)	16.3 pF/ft (53.5 pF/m)	75 Ohm	82%

Voltage

Voltage Rating
300 V RMS

Electrical Characteristics Notes: Return Loss: Fixed bridge and termination

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	-30°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
1.59 in (40.4 mm)	1.59 in (40.4 mm)

Max. Pull Tension: 40 lbs (18 kg)

Bulk Cable Weight: 17 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Euroclass Dca, Indoor, Aerial - Black only, When supported by messenger wire
CPR Compliance:	CPR Euroclass: Dca-s1,d1,a1; CPR UKCA Class: Dca-s1,d1,a1
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes: Print legend includes sequential footage marks.

History

Update and Revision: Revision Number: 0.198 Revision Date: 04-29-2024

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
--------	-------	------------	--------	-----

4855ANH G753280	Aqua	Reel	100 m	612825443452
4855ANH G751000	Aqua	Reel	305 m	612825443353
4855ANH G751640	Aqua	Reel	500 m	612825443407
4855ANH 0103280	Black	Reel	100 m	612825443490
4855ANH 0101000	Black	Reel	305 m	612825443391
4855ANH 0101640	Black	Reel	500 m	612825443445
4855ANH 0063280	Blue	Reel	100 m	612825443476
4855ANH 0061000	Blue	Reel	305 m	612825443377
4855ANH 0061640	Blue	Reel	500 m	612825443421
4855ANH N3U3280	Green	Reel	100 m	612825443469
4855ANH N3U1000	Green	Reel	305 m	612825443360
4855ANH N3U1640	Green	Reel	500 m	612825443414
4855ANH 0071000	Purple	Reel	305 m	612825443384
4855ANH 0071640	Purple	Reel	500 m	612825443438

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.