



Product: [5001UE](#) 



Security & Sound, 3 Conductor 12 AWG BC, Riser

Product Description

Security & Commercial Audio Cable, 3 Conductor 12 AWG stranded (19x25) bare copper conductors with polyolefin insulation, Riser, PVC jacket with ripcord.

Technical Specifications

Product Overview

Suitable Applications:	Intercom/PA Systems, Sound/Audio Systems
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
12	19x25	BC - Bare Copper	3

Conductor Count:	3
------------------	---

Insulation

Material	Nominal Wall Thickness
PP - Polypropylene	0.011 in

Color Chart

Number	Color
1	Black
2	White
3	Red

Outer Shield

Material
No Shield

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.277 in	0.017 in	Yes

Construction and Dimensions

Cabling

Twists
2.526 twist/ft

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
1.6 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor

24 pF/ft

Current

Max. Recommended Current [A]

12 Amps per Conductor at 25°C

Voltage

UL Voltage Rating

300 V RMS

Temperature Range

UL Temp Rating: 75°C

Operating Temp Range: -20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight: 78.5 lbs/1000ft

Max. Pull Tension: 228 lbs

Min. Bend Radius/Minor Axis: 2.8 in

Standards

NEC Articles: Article 725

NEC/(UL) Compliance: CL3R

Applicable Environmental and Other Programs

Environmental Space: Indoor - Riser

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2003/96/EC (BFR): Yes

EU Directive 2011/65/EU (RoHS 2): Yes

EU Directive 2012/19/EU (WEEE): Yes

EU Directive Compliance: EU Directive 2003/11/EC (BFR)

EU CE Mark: Yes

MII Order #39 (China RoHS): Yes

Flammability, LS0H, Toxicity Testing

UL Flammability: UL1666 Vertical Riser

CSA Flammability: FT4

UL voltage rating: 300 V RMS

Plenum/Non-Plenum

Plenum (Y/N): No

Plenum Number: 6001UE

Part Number

Variants

Item #	Color	Put-Up Type	Length	UPC
5001UE 0081000	Gray	Reel	1,000 ft	612825155706

Footnote: C - CRATE REEL PUT-UP.

History

Update and Revision: Revision Number: 0.346 Revision Date: 08-27-2021

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.