



REPRESENTATIVE IMAGE

**Product:** [5100UE](#)

Security & Sound, 2 Conductor 14 AWG BC, CL3R, FPLR

## Product Description

Security & Commercial Audio Cable, Riser-CL3R-FPLR 2-14 AWG stranded bare copper conductors with polypropylene insulation, PVC jacket with ripcord

## Technical Specifications

### Product Overview

Suitable Applications:	Intercom/PA Systems, Sound/Audio Systems, Fire Alarm (For color Red only)(Dual Rated)
------------------------	---

### Construction Details

#### Conductor

Element	Number of Element	Size	Stranding	Material
Conductor(s)	2	14 AWG	19x26	BC - Bare Copper

#### Insulation

Element	Material	Nom. Thickness	Color Code
Conductor(s)	PP - Polypropylene	0.011 in (0.28 mm)	Black, White

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.017 in (0.43 mm)	0.218 in (5.54 mm)	Yes

Overall Cable Diameter (Nominal):	0.218 in (5.54 mm)
-----------------------------------	--------------------

### Electrical Characteristics

#### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Conductor(s)	2.53 Ohm/1000ft (8.30 Ohm/km)	22 pF/ft (72 pF/m)	8 Amps per conductor @ 25°C

#### Voltage

UL Voltage Rating
300 V (CL3R, FPLR)

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating
75°C	-20°C to +75°C

#### Bend Radius

Stationary Min.	Installation Min.
2.2 in (56 mm)	2.2 in (56 mm)

Max. Pull Tension:	95 lbs
Bulk Cable Weight:	33 lbs/1000ft (49 kg/km)

### Standards and Compliance

Environmental Suitability:	Indoor - Riser, Indoor
Flammability / Reaction to Fire:	UL1666 Riser, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 725, Article 760, CL3R, FPLR
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	6100UH

## History

Update and Revision:	Revision Number: 0.354 Revision Date: 12-15-2021
----------------------	--

## Variants

Item #	Color	Putup Type	Length	UPC/EAN
5100UE 0101000	Black	Reel	1,000 ft	612825423324
5100UE 010Z1000	Black	ReelTuff Box	1,000 ft	612825156369
5100UE.00152	Chrome	Reel	152 m	8719605007742
5100UE.00305	Chrome	Reel	305 m	8719605007759
5100UE.00U305	Chrome	Reel	305 m	8719605007773
5100UE.00500	Chrome	Reel	500 m	8719605007766
5100UE 008500	Gray	Reel	500 ft	612825156314
5100UE 0081000	Gray	Reel	1,000 ft	612825156338
5100UE 008U1000	Gray	UnReel	1,000 ft	612825423317
5100UE 008Z1000	Gray	ReelTuff Box	1,000 ft	612825156345
5100UE 0021000	Red	Reel	1,000 ft	612825423300
5100UE 002Z1000	Red	ReelTuff Box	1,000 ft	612825156321

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.