



Product: [5442FE](#)

Security & Sound, #20-3pr, BC, Shielded, CMR

Product Description

Security & Sound Cable, Riser-CMR, 3-20 AWG stranded bare copper pairs with polypropylene insulation, Beldfoil® shield and PVC jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls, Noisy Environment
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
20	7x28	BC - Bare Copper	3

Conductor Count:	6
------------------	---

Insulation

Material	Nominal Wall Thickness
PP - Polypropylene	0.007 in

Color Chart

Number	Color
1	Black & Red
2	Black & White
3	Black & Green

Outer Shield Material

Material	Material Trade Name	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Bi-Laminate (Alum+Poly)	Beldfoil®	TC - Tinned Copper	24	7x32

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.232 in	0.017 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
10.3 Ohm/1000ft	10.5 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
26 pF/ft	46.8 pF/ft

Current

Max. Recommended Current [A]
2.6 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Operating Temp Range:	-20°C To +75°C
-----------------------	----------------

Mechanical Characteristics

Bulk Cable Weight:	26.9 lbs/1000ft
Max. Pull Tension:	84.7 lbs
Min. Bend Radius/Minor Axis:	2.4 in

Standards

NEC/(UL) Compliance:	CMR
CEC/C(UL) Compliance:	CMG

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1666 Riser
CSA Flammability:	FT4
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	6442FE

Part Number

Variants

Item #	Color	UPC
5442FE 0081000	Gray	612825162551
5442FE 008U1000	Gray	612825162544

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.295 Revision Date: 08-27-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.