



**Product:** [5504F1](#)

Security & Sound, #22-6c, TC, Shielded, CM, Water-Blocked

### Product Description

Security & Sound Cable, Rated-CM, 6-22 AWG stranded tinned copper conductors with PVC insulation, waterblocking tape, Beldfoil® shield and PVC jacket with ripcord

### Technical Specifications

#### Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls, Noisy & Wet Location, Below-Grade Duct
------------------------	---

#### Construction Details

##### Conductor

Element	Number of Element	Size	Stranding	Material
Conductor(s)	6	22 AWG	7x30	TC - Tinned Copper

##### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.011 in (0.28 mm)	0.051 in (1.3 mm)	Black, Red, White, Green, Brown, Blue

##### Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

##### Outer Jacket

Separator	Material	Nom. Thickness	Nom. Diameter	Ripcord
Waterblocking Tape	PVC - Polyvinyl Chloride	0.025 in (0.64 mm)	0.238 in	Yes

Overall Cable Diameter (Nominal): 0.238 in

#### Electrical Characteristics

##### Electricals

Nom. Conductor DCR	Max. Current
17.9 Ohm/1000ft	2 Amps per Conductor at 25°C

##### Voltage

UL Voltage Rating
300 V

#### Mechanical Characteristics

##### Temperature

UL Temperature	Operating
105°C	-30°C To +105°C

##### Bend Radius

Stationary Min.	Installation Min.
2.38 in (60.5 mm)	2.38 in

Max. Pull Tension:	60.1 lbs (27.3 kg)
Bulk Cable Weight:	30 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Outdoor - Water Exposure, Indoor, Outdoor
Flammability / Reaction to Fire:	UL1685 UL Loading
NEC / UL Compliance:	Article 800, CM
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2019-05-03
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision:	Revision Number: 0.50 Revision Date: 04-08-2022
----------------------	---

## Part Numbers

### Variants

Item #	Color	Putup Type	Length
5504F1 0101000	Black	Reel	1,000 ft

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.