



Product: [5626UG](#)

Nurse Call & Paging, #24-8c, BC, Unshielded, CM

Product Description

Nurse Call & Paging Cable, Rated-CM, 8-24 AWG solid bare copper conductors with polyolefin insulation, PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	Nurse Call, Commercial Sound, Annunciators, Voice Systems, Paging
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Conductors
24	Solid	BC - Bare Copper	0.020 in	8

Conductor Count:	8
------------------	---

Insulation

Material	Nominal Diameter
PP - Polypropylene	0.033 in

Color Chart

Number	Color
1	Yellow
2	Blue
3	Black
4	Orange
5	Red
6	Green
7	White
8	Purple

Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	.093 x .324 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
25.9 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor
17 pF/ft

Current

Max. Recommended Current [A]

1.4 Amps per Conductor at 25°C (10°C Temperature Rise)

Voltage

UL Voltage Rating

300 V RMS

Temperature Range

Operating Temp Range: -25°C To +75°C

Mechanical Characteristics

Bulk Cable Weight: 25 lbs/1000ft

Max. Pull Tension: 32 lbs

Standards

NEC/(UL) Compliance: CM

CEC/C(UL) Compliance: CM

Applicable Environmental and Other Programs

Environmental Space: Indoor Rated (Not Riser or Plenum)

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2003/11/EC (BFR): Yes

EU Directive 2011/65/EU (ROHS II): Yes

EU Directive 2012/19/EU (WEEE): Yes

EU Directive 2015/863/EU: Yes

EU Directive Compliance: EU Directive 2003/11/EC (BFR)

EU RoHS Compliance Date (yyyy-mm-dd): 2005-07-01

MII Order #39 (China RoHS): Yes

Suitability

Suitability - Aerial: Yes - Black only, when supported by messenger wire

Suitability - Burial: No

Suitability - Hazardous Locations: No

Suitability - Indoor: Yes

Suitability - Outdoor: Yes - Black only

Flammability, LSOH, Toxicity Testing

UL Flammability: UL1685 UL Loading

UL voltage rating: 300 V RMS

Plenum/Non-Plenum

Plenum (Y/N): No

Plenum Number: 6626UG

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
5626UG F6H1000	Gray, Dark Pearl	Reel	1,000 ft	612825164807

Footnote: C - CRATE REEL PUT-UP.

History

Update and Revision: Revision Number: 0.267 Revision Date: 06-08-2020

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and

regulations based on their individual usage of the product.