

Product: [70069CH](#) 



2 PAIR AES/EBU, 22AWG, ISTP, LSZH-C

Product Description

DIGITAL AUDIO 2 PAIR AES/EBU, 22AWG/0.34mm², ISTP, LSZH-C

Technical Specifications

Product Overview

Suitable Applications:	Digital multi-modulation cable used in professional studios for the transmission of analogue and digital audio signals.; Designed to meet the requirements of the AES/EBU specification
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
22	7x30	BC-OFHC - Oxygen-Free Bare Copper (High Conductivity)	2

Conductor Count:	4
Total Number of Pairs:	2

Insulation

Material	Nominal Diameter	Diameter +/- Tolerance
PE - Polyethylene (Foam)	2.1 mm	0.05 mm

Color Chart

Number	Color
Pair 1 t/m 2	Red & Black

Inner Shield Material

Type	Material	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Position
Tape	Bi-Laminate (Alum+Poly)	100%	Stranded tinned copper	22	Under shielding foil

Inner Jacket Material

Material	Nominal Diameter	Diameter +/- Tolerance
LSZH - Low Smoke Zero Halogen (Flame Retardant)	5.3 mm	0.1 mm

Table Notes:	Elements are numbered for identification
--------------	--

Outer Shield Material

Material
Bi-Laminate (Alum+Poly)

Outer Jacket Material

Material	Nominal Diameter	Diameter +/- Tolerance
LSZH - Low Smoke Zero Halogen (Flame Retardant)	13.5 mm	0.1 mm

Construction and Dimensions

Cabling

Description
1 center filler + 2 pairs + stranded tinned copper drainwire (22AWG)(7x0.25) covered with a non-woven foil

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR

86 Ohm/km

Capacitance

Nom. Capacitance Conductor to Conductor

40 pF/m

Impedance

Nominal Characteristic Impedance

110 Ohm

Nominal Characteristic Tolerance

15 Ohm

Temperature Range

Other Temp Range: -30-+70 °C

Mechanical Characteristics

Min Setting Radius: 67.5 mm

Standards

CPR Euroclass: Dca-s1,d1,a1

Applicable Environmental and Other Programs

Environmental Space: Indoor - Euroclass Dca

EU RoHS Compliance Date (yyyy-mm-dd): 2014-12-01

Flammability, LSOH, Toxicity Testing

IEC Flammability: IEC 60332-1-2 and IEC 60332-3-24

IEC 60754-1 (EN50267-1)- Halogen Amount: Zero

Part Number

Variants

Item #	Color	Putup Type	Length	EAN
70069CH.00500	Gray	Reel	500 m	8719605124272

History

Update and Revision: Revision Number: 0.113 Revision Date: 08-25-2020

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.