



**Product:** [7107W](#)

MachFlex™, 17+1G C #20 Str BC, PVC Ins, TPE Jkt, PLTC

[Request Sample](#)

**Product Description**

MachFlex™ for High Flex, 17+1G Conductor 20AWG (74x38) Bare Copper, PVC Insulation, TPE Outer Jacket, PLTC

**Technical Specifications**

**Construction Details**

**Conductor**

Element	Number of Element	Size	Stranding	Material
Conductor(s)	17	20 AWG	74x38	BC - Bare Copper
Ground Wire	1	20 AWG	74x38	BC - Bare Copper

**Insulation**

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.074 in (1.9 mm)	Black and Numbered
Ground Wire	PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.074 in (1.9 mm)	Green/Yellow

**Outer Shield**

Material
No Shield

**Outer Jacket**

Separator	Material	Nom. Thickness	Nom. Diameter
non-Woven Tape	TPE - Thermoplastic Elastomer	0.053 in (1.3 mm)	0.48 in

Overall Cable Diameter (Nominal): 0.48 in

**Electrical Characteristics**

**Electricals**

Element	Nom. Conductor DCR	Max. Current
Conductor(s)	10.8 Ohm/1000ft	5.4 Amps per Conductor at 30°C
Ground Wire	10.7 Ohm/1000ft (35.1 Ohm/km)	14.4 Amps per Conductor at 30°C

**Voltage**

UL Voltage Rating	Voltage Rating
300 V	600 V

**Mechanical Characteristics**

**Temperature**

UL Temperature	Operating
UL : 90°C, AWM 20327 : 105°C	-40°C To 105°C

**Bend Radius**

Stationary Min.	Installation Min.
4.8 in (120 mm)	4.8 in

Max. Pull Tension: 226.8 lbs

Bulk Cable Weight:	140 lbs/1000ft
--------------------	----------------

## Standards and Compliance

Environmental Suitability:	Outdoor, Sunlight Resistance, UV Resistance, Oil Resistance
Flammability / Reaction to Fire:	UL1685 UL Loading, FT2, IEEE 1202 FT4
NEC / UL Compliance:	Article 725, PLTC
AWM Compliance:	UL AWM Style 20327, AWM I/II A/B
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision:	Revision Number: 0.369 Revision Date: 12-20-2021
----------------------	--

## Variants

Item #	Color	Putup Type	Length	UPC
7107W 003250	Orange	Reel	250 ft	612825182078
7107W 0031000	Orange	Reel	1,000 ft	612825182061
7107W 0035000	Orange	Reel	5,000 ft	612825182085

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.