



Product: [7953A](#)

DataTuff® Cat 6, 4 Bonded-Pr #23 Sol BC, PO Ins, OS, PVC Jkt, PVC Jkt, MSHA, CMX-Outdoor 600V AWM 21047

[Request Sample](#)

Product Description

Industrial Ethernet Cat 6, 4 Bonded-Pair 23AWG (Solid) Bare Copper, PO Insulation, Overall Beldfoil® Shield, PVC Inner Jacket, PVC Outer Jacket, MSHA, CMX-Outdoor 600V AWM 21047

Technical Specifications

Product Overview

Suitable Applications:	Outdoor, in cabinet with high volt devices, such as motor control center, mining, noisy environment, harsh environment, IIoT, factory or process automation, IP cameras and devices, data communication, PoE++, PoE+, PoE, etc.
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/patents .

Construction Details

Conductor

Element	Size	Stranding	Material	No. of Elements
Pair(s)	23 AWG	Solid	BC - Bare Copper	4

Insulation

Material	Color Code
PO - Polyolefin	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown

Bonded-Pair:	Yes
--------------	-----

Inner Jacket

Material	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.254 in (6.45 mm)	Yes

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

Outer Jacket

Separator	Material	Nom. Diameter
Center Member (Patented X-Spline®)	PVC - Polyvinyl Chloride	0.335 in (8.51 mm)

Overall Cable Diameter (Nominal):	0.335 in (8.51 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Capacitance Unbalance
82 Ohm/km (25 Ohm/1000ft)	330 pF/ft

Delay

Max. Delay	Max. Delay Skew	Nom. Velocity of Prop.
537 ns/100m	45 ns/100m	72%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted) [Ohm]	Max./Min. Fitted Impedance [Ohm]
1	2.0 dB/100m	74.3	72.3	72.3	70.3	67.8	64.8	21	100 ± 15	100 ± 15
4	3.8 dB/100m	65.3	63.3	61.5	59.5	55.8	52.7	24	100 ± 15	100 ± 15
8	5.3 dB/100m	60.8	58.8	55.4	53.4	49.7	46.7	25.5	100 ± 15	100 ± 15
10	6 dB/100m	59.3	57.3	53.3	51.3	47.8	44.8	26	100 ± 15	100 ± 15
16	7.6 dB/100m	56.2	54.3	48.7	46.7	43.7	40.7	26	100 ± 15	100 ± 15
20	8.5 dB/100m	54.8	52.8	46.3	44.3	41.8	38.8	26	100 ± 15	100 ± 15
25	9.5 dB/100m	53.3	51.3	43.8	41.8	39.8	36.8	25.3	100 ± 15	100 ± 15
31.25	10.7 dB/100m	51.9	49.9	41.2	39.2	37.9	34.9	24.6	100 ± 15	100 ± 15
62.5	15.4 dB/100m	47.4	45.4	32	30	31.9	28.9	22.5	100 ± 15	100 ± 15
100	19.8 dB/100m	44.3	42.3	24.5	22.5	27.8	24.8	21.1	100 ± 15	
155	25.2 dB/100m	41.5	39.5	16.3	14.3	23.9	20.9	19.8	100 ± 22	
200	29.0 dB/100m	39.8	37.8	10.8	8.8	21.8	18.8	19	100 ± 22	
250	32.8 dB/100m	38.3	36.3	5.5	3.5	19.8	16.8	18.3	100 ± 32	

Voltage

UL Voltage Rating
300 V (CMR, CMX-Outdoor), 600 V (AWM 21047)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation	Storage
90°C	-40°C To +90°C	-25°C To +75°C	-40°C To +80°C

Bend Radius

Stationary Min.
4 in (100 mm)

Max. Pull Tension:	40 lbs (18 kg)
Bulk Cable Weight:	47 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance, Oil Resistance, Aerial
Flammability / Reaction to Fire:	UL1666 Riser, FT4, IEEE 1202 Vertical Tray Flame Test, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 800, CMR, CMX-Outdoor
AWM Compliance:	AWM 21047
CEC / C(UL) Compliance:	CMX-Outdoor;CMG
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
NEMA Compliance:	ANSI/NEMA WC-66
Data Category:	Category 6
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 6
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61156-5
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Operating temperatures are subject to length de-rating. Cable passes -40C Cold Bend per UL 1581. Not intended for 600 V electrical power delivery. T568A Plug Compatible Part Number: R301601. T568B Plug Compatible Part Number: R301602 T568B Plug Compatible.
--------	--

History

Update and Revision:	Revision Number: 0.532 Revision Date: 12-12-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
--------	-------	------------	--------	-----	----------

7953A 0101000	Black	Reel	1,000 ft	612825191964	C
7953A 0105000	Black	Reel	5,000 ft	612825191971	C
7953A 0061000	Blue	Reel	1,000 ft	612825191940	C
7953A 0081000	Gray	Reel	1,000 ft	612825191957	C
7953A 0021000	Red	Reel	1,000 ft	612825191933	C
7953A 1NH1000	Teal	Reel	1,000 ft	612825191988	C

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.