



Product: [83905](#)

Type K Thermocouple, 1 Pr #20 Sol, FEP Ins Yel, Red, Brn FEP Jkt, CL3P 200C PLTC SUN RES

[Request Sample](#)

Product Description

Type K Thermocouple, 1 Pair 20AWG (Solid) Chromel+Alumel, FEP Insulation Yel, Red Color Code, Brown FEP Outer Jacket, CL3P 200C PLTC SUN RES

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
20	Solid	Chromel & Alumel	1

Conductor Count:

Insulation

Material	Nominal Wall Thickness
FEP - Fluorinated Ethylene Propylene	0.01 in

Color Chart

Number	Color
Chromel	Yellow
Alumel	Red

Outer Shield Material

Material
No Shield

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
FEP - Fluorinated Ethylene Propylene	0.076 x 0.128 in	0.012 in

Electrical Characteristics

Conductor DCR

Element	Nominal Conductor DCR
Chromel	420 Ohm/1000ft
	169 Ohm/1000ft

Temperature Range

UL Temp Rating:	200°C
Operating Temp Range:	-70°C To +200°C

Mechanical Characteristics

Bulk Cable Weight:	13 lbs/1000ft
Min Bend Radius/Minor Axis:	1.25 in

Standards

NEC/(UL) Compliance:	CL3P, PLTC
----------------------	------------

Data Category:	MC 96.1-1982 Type K
ANSI Compliance:	MC 96.1-1982 Type K

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Sunlight Resistance:	Yes
------------------------------------	-----

Flammability, LSOH, Toxicity Testing

UL Flammability:	NFPA 262, UL 910 (Plenum)
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
83905 001100	Brown	Reel	100 ft	612825205852
83905 001500	Brown	Reel	500 ft	612825205876
83905 0011000	Brown	Reel	1,000 ft	612825205869

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

Product Notes

Notes:	Chromel & Alumel = ""Chromel and Alumel are Hoskins Manufacturing Company trademarks.""
--------	---

History

Update and Revision:	Revision Number: 0.306 Revision Date: 07-09-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.