



Product: [9867](#)

Lead Wire, #20 Str TC, Conductive PO/PO Ins, PVC Jkt, AWM 3239

Request Sample

### Product Description

Low Temp Plastic Lead Wire, 20AWG (7x28) Tinned Copper, Conductive PO/PO Insulation, PVC Outer Jacket, AWM 3239 80C

### Technical Specifications

#### Product Overview

Suitable Applications:	internal wiring of electronic equipments, high voltage applications
------------------------	---

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	No. of Conductors
20	7x28	TC - Tinned Copper	1

Conductor Count:	1
------------------	---

##### Insulation

Material	Nominal Wall Thickness
PE - Polyethylene	0.051 in

Table Notes:	.003 in. conductive polyethylene over stranding.
--------------	--

##### Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.201 in	0.028 in

#### Electrical Characteristics

##### High Frequency (Nominal/Typical)

Nom. Insertion Loss
6 dB/100m
6 dB/100m
6 dB/100m
6 dB/100m

##### Unbalanced Crosstalk

Typical Unbalanced NEXT %
6 MHz

##### Voltage

Breakdown Voltage	Non-UL Description	Non-UL Voltage Rating	UL Voltage Rating
60,000 V (DC)	AC (60 Hertz)	11,000 V RMS	30,000 V DC

#### Temperature Range

UL Temp Rating:	80°C
Operating Temperature Range:	-30°C To +80°C

#### Mechanical Characteristics

Bulk Cable Weight:	19 lbs/1000ft
Max. Pull Tension:	15 lbs
Min. Bend Radius/Minor Axis:	3 in

## Standards

UL AWM Style Compliance:	AWM 3239
--------------------------	----------

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
CA Prop 65:	Yes
MII Order #39 (China RoHS):	Yes

## Flammability, LSOH, Toxicity Testing

UL Flammability:	VW-1
UL voltage rating:	30,000 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Related Part Numbers

### Variants

Item #	Color	Put-Up Type	Length	UPC
9867 002500	Red	Reel	500 ft	612825259749

## History

Update and Revision:	Revision Number: 0.395 Revision Date: 04-08-2022
----------------------	--

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.