



Product: [ACX-01RM-048P-U](#)



FiberExpress ACX HD Patch Panel Housing, Full Front Sliding Drawer, 1U

Product Description

FiberExpress High Density Patch Panel Housing with Full Front Sliding Drawer, 1U/19", Empty, Black

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers

Construction

Weight:	4.8 kg
Height:	44 mm
Width:	482 mm
Depth:	398 mm

Physical Specifications

Max Capacity:	Support up to 4 ACX series cassettes or adaptor frame (Up to 96 fibers per U)
---------------	---

Temperature Range

Operating Temperature Range:	-10°C to +60°C
Storage Temperature Range:	-40°C to +70°C

Product Material

Materials

Material
SPCC

Standards

EU Directive 2011/65/EU (RoHS 2):	Yes
-----------------------------------	-----

Related Part Numbers

Included Parts:	Cage nuts and Screw; Velcro Tapes; Port Identification Adhesive Label
Related Parts:	FiberExpress ACX High Density Cassettes (ACX-FCxxxx) ACX High Density Adaptor Strip (ACX-FFxxxx), Blank Plate (ACX-FF-BLANK) for unoccupied ports

Variants

Item #	Color
ACX-01RM-048P-U	Black

Product Notes

Packaging:	Individually packaged in a cardboard box
Notes:	Access : Full Front Sliding Drawer

History

Update and Revision:	Revision Number: 0.14 Revision Date: 04-13-2025
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.