

Product: [ACX-01RM-048P](#) 



FX ACX 1U/19" HD Patch Panel Housing, 4 slots, Empty, Black

Product Description

FX ACX 1U/19" HD Patch Panel Housing, 4 slots, Empty, Black

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	FiberExpress Solutions, Backbone, Data Centers, Main Distribution Room, Telecommunications Room

Material

Weight:	4.4 kg
Overall Height:	43.5 mm
Overall Width:	482.6 mm
Overall Depth:	400 mm

Physical Specifications

Max Capacity:	Holds 4 ACX cassettes
---------------	-----------------------

Temperature Range

Operating Temperature Range:	-10°C to +60°C
Storage Temperature Range:	-40°C to +70°C

Product Material

Materials

Element	Description
Steel	Panel
Steel	Front door

Standards

EU Directive 2011/65/EU (RoHS 2):	Yes
-----------------------------------	-----

Related Part Numbers

Included Parts:	Cage nuts and screw; Velcro Tapes; Port identification Adhesive Label; Self-adhesive patch cord management clamp
Related Parts:	FiberExpress ACX High Density Cassettes (ACX-FCxxxx), ACX High Density Adaptor Strip (ACX-FFxxxx), Blank Plate (ACX-FF-BLANK) for unoccupied ports

Product Notes

Packaging:	Individually packaged in a cardboard box
Notes:	Access: Front and Rear Sliding Drawer, this design is not applicable to splicing application

History

Update and Revision:	Revision Number: 0.18 Revision Date: 04-21-2025
----------------------	---

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.