



Product: [ACX-FFxSyyM8z](#)

FX ACX Adapter Frame SM & MM MPO 16 (Offset key) Key up/Key Down (Type A)

Product Description

FX ACX Adapter Frame SM & MM MPO 16 (Offset key) Key up/Key Down (Type A)

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers

Temperature Range

Operating Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-10°C To +75°C

Product Material

Materials

Description	Material	Color
Frame Base Material	SPCC	Black
Frame Surface Treatment	Powder Coating	
Adaptor Type	MPO-16	Black

Standards

TIA/EIA Compliance:	TIA-568.3-E, TIA/EIA-604-5(FOCIS-5)
ISO/IEC Compliance:	IEC 11801
EU Directive 2011/65/EU (RoHS 2):	Yes

Related Part Numbers

Related Parts:	FX ACX HD Patch Panel Housing (Part Number: ACX-01RM-048P-U)
----------------	--

Variants

Item #	Port Count
ACX-FFXS04M8N	4 Port
ACX-FFXS06M8N	6 Port

Product Notes

Packaging:	Individually packaged in a sealed plastic bag.
------------	--

History

Update and Revision:	Revision Number: 0.2 Revision Date: 08-18-2025
----------------------	--

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.