



Product: [AP106503](#)



KeyConnect Shielded and Unshielded Patch Panel with Shutter, 24-Port, 1U, Black (Empty)

Product Description

KeyConnect Shielded and Unshielded Patch Panel with Shutter, 24-Port, 1U Flat Style, Black (Empty)

Technical Specifications

Product Overview

Suitable Applications:	Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800, 3600, 2400 and 1200.
------------------------	--

Physical Characteristics (Overall)

Height:	44.5 mm
Width:	482.6 mm
Depth:	110 mm
Port Count:	24 Port
Front Connection:	Flush
Packaging:	Individually packaged in a cardboard box.
Weight:	0.8 kg

Connectors

Materials

Description	Material
Panel Body	SPCC
Transparent Shutter & Label Holder	PC
Black Plastic	ABS

Construction and Dimensions

Max Capacity:	24 connectors
---------------	---------------

Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

Applicable Environmental and Other Programs

EU Directive 2011/65/EU (RoHS 2):	Yes
-----------------------------------	-----

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Related Part Numbers

Related Parts:	Compatible with 10GX, CAT6+ and CAT5E KeyConnect Modular Jacks, REVConnect Modular Jacks as well as KeyConnect Multimedia Modules.
----------------	--

Variants

Item #	Color	Putup Type
AP106503	Black	1U

Product Notes

Included Parts:	4 Screws (M6*16); 4 M6 Nuts; 1 Ground Wire(200mm), Rear Cable Management Bar, Cable Ties
Notes:	For proper installation refer to Installation Guide PX105408 included with the product

History

Update and Revision:	Revision Number: 0.29 Revision Date: 04-08-2022
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.