



Product: [BB3PHCTD6](#) 

Micro BNC Crimping Tool for 4855RMBUHD3, 4855EMBUHD3, 4505RMBUHD3, 4694RMBUHD3

Product Description

Micro BNC Crimping Tool for 4855RMBUHD3, 4505RMBUHD3, & 4694RMBUHD3

Technical Specifications

Product Overview

Suitable Applications:	To crimp Micro BNC connectors
------------------------	-------------------------------

Connectors

Materials

Description	Material	Color
Frame	Steel	
Handle grip	Steel	Blue
	Steel	
	Steel	

Temperature Range

Installation Temperature Range:	-10°C To +50°C
Storage Temperature Range:	-40°C To +60°C

Mechanical Characteristics

Dimensions (WxHxD)

Length	Height
254.000 mm	76.200 mm

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2011/65/EU (RoHS 2):	Yes

Related Part Numbers

Variants

Item #	Color
BB3PHCTD6	Blue

Footnote:	Q - STANDARD PACKAGES CANNOT BE BROKEN.
-----------	-----------------------------------------

History

Update and Revision:	Revision Number: 0.7 Revision Date: 04-08-2022
----------------------	------------------------------------------------

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.