

Product: [BHDO Annual Subscription, Scale Tier](#) 



BHDO Annual Subscription, Scale Tier

Product Description

Belden Horizon Data Operations (BHDO) enables collection of OT data for contextualization at the edge and then transfers the data to IT systems for storage, visualization, and analysis. This is an annual subscription for the "Scale" license that may be used to deploy BHDO on one (1) site. Belden Horizon Data Manager (BHDM) access is included in this package.

Technical Specifications

Product description

Type:	Belden Horizon Data Operations (BHDO)
Name:	BHDO Annual Subscription, Scale Tier
Part Number:	BHDO-SITE-SCALE
Sites:	1
Nodes:	Unlimited
Data Points:	50000
Devices:	Unlimited
License:	A valid 1 site full license for BHDO + access to BHDM
Processor:	Intel x86 64-bit processor 16 Core@2.2Ghz (Example: Intel i5)
Validity:	12 months from the order of license

Hardware

Memory:	16 GB RAM
Storage:	80 GB available space

Hardware Requirements

Memory (RAM) (minimum):	8-16 GB
Storage (Disc) (minimum):	100-250 GB
NIC (Network Interface):	At least two (one for IT network, one for OT network)

Configuration Parameters

Devices (minimum):	1
Average Tags per Device:	10 - 20+
Flows Instances:	0-4'
Average Flow Nodes:	10+
Applications/Containers:	0-2+
Analytics:	0-5+
Integrations:	1+
Cores:	4+
InfluxDB Usage:	Mandatory with in-stream processing

Scope of delivery and accessories

Scope of delivery:	Software deployed via containers and/or virtual machines under licensing model
--------------------	--

Further Instructions

Product Documentation:	https://docs.belden.io/bhdo/
Installation Guide:	https://docs.belden.io/bhdm/installation-and-deployments

History

Update and Revision:	Revision Number: 0.47 Revision Date: 04-24-2025
----------------------	---

Variants

Item #	Type
BHDO-SITE-SCALE	BHDO SITE-BASED SCALE TIER

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.