

Product: [CAT5E REVConnect Panel 24P](#) 

CAT5e REVConnect Patch Panel, 24 Port



Product Description

CAT5E REVConnect Patch Panel, Flat, 24-Port, 1U (Preloaded)

Technical Specifications

Product Overview

Suitable Applications:	1200 System, TIA Category 5E, ISO Class D, 1GBASE-T
------------------------	---

Physical Characteristics (Overall)

Height:	1.73 in
Width:	19.000 in
Depth:	2.000 in
Port Count:	24 Port
Front Connection:	Flush
Packaging:	Individually packaged in a cardboard box.
Weight:	1.846 lbs

Connectors

Materials

Description	Material	Color
Panel	Steel	Black/White
Frame	PC/ABS	Black/White
Management Bar	Steel	Black
Clear Window	Polycarbonate	Transparent

Construction and Dimensions

Max Capacity:	24 connectors (preloaded)
---------------	---------------------------

Electrical Characteristics

Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute (Signals to Ground)
Current Rating:	1.300 A
Insulation Resistance:	500 M-Ohm Minimum
Termination Resistance:	2.5 mOhm

Temperature Range

Installation Temp Range:	-10°C To +60°C
Storage Temp Range:	-40°C To +70°C
Operating Temp Range:	-10°C To +60°C

Mechanical Characteristics

Footprint/Type:	REVConnect
Tool Compatibility:	REVConnect Termination Tool (RVUTT01)
Plug /Jack Compatibility:	RJ45

Cable/Connector Retention:	15 lbs
Connector/Hardware Retention:	20 lbs
Plug/Connector Retention:	11.250 lbs

Standards

UL Rating:	UL94V-0
IEC Compliance:	IEC 60603-7
Data Category:	Category 5e
TIA/EIA Compliance:	Category 5e - TIA 568.2-D, ISO/IEC 11801-1
IEEE Compliance:	Power Over Ethernet (PoE) IEEE 802.3at type 1 and 2 (up to 30W), IEEE802.3bt/D1.7 type 3 and 4 (up to 100W), CISCO UPOE (up to 60W), Power over HDBase TTM (up to 100W)
Other Compliance:	UL 1863, IEC 60603-7, ANSI/TIA 1096-A (formerly FCC Part 68-F)

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2011/65/EU (ROHS II):	Yes
MII Order #39 (China RoHS):	EUP 50

Flammability, LS0H, Toxicity Testing

Safety Listing:	c(UL)us Listed
-----------------	----------------

Part Number

Related Parts:	CAT5E REVConnect Modular Jacks, CAT5E Modular Cords
----------------	---

Variants

Item #	Color	UPC
RV5PPF1U24BK	Black	611589224895

Product Notes

Included Parts:	24 Cat5E UTP REVConnect Jacks, 25 REVConnect Cores, 4 Screws (10x32); 4 Clear Windows; 1 Rear Cable Management Bar; 4 Screws (12x24); 2 Velcro Straps; 1 Installation Guide
Notes:	For proper installation refer to Installation Guide PX106520 included with the product

History

Update and Revision:	Revision Number: 0.39 Revision Date: 03-12-2020
----------------------	---

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.