



Product: [CAT5E UTP CMP BONDED PIGTAILS](#)

CAT5E Pigtail, Bonded, UTP, CMP



Product Description

CAT5E Copper Pigtail, Bonded, UTP, CMP

Technical Specifications

Standards

Data Category:	Category 5e
----------------	-------------

Applicable Environmental and Other Programs

Environmental Space:	Indoor
----------------------	--------

Related Part Numbers

Variants

Item #	Color	Length
C502206015	Blue	15 ft
C502206020	Blue	20 ft
C502206025	Blue	25 ft
C502206035	Blue	35 ft
C502206050	Blue	50 ft
C502206075	Blue	75 ft
C502206100	Blue	100 ft
C502306010	Blue	10 ft
C502306015	Blue	15 ft
C502306020	Blue	20 ft
C502306025	Blue	25 ft
C502306030	Blue	30 ft
C502306035	Blue	35 ft
C502306040	Blue	40 ft
C502306050	Blue	50 ft
C502306060	Blue	60 ft
C502306070	Blue	70 ft
C502306075	Blue	75 ft
C502306100	Blue	100 ft
C502208015	Gray	15 ft
C502208020	Gray	20 ft
C502208025	Gray	25 ft
C502208035	Gray	35 ft
C502208050	Gray	50 ft
C502208075	Gray	75 ft
C502208100	Gray	100 ft
C502308015	Gray	15 ft
C502308020	Gray	20 ft
C502308025	Gray	25 ft
C502308030	Gray	30 ft

C502308035	Gray	35 ft
C502308050	Gray	50 ft
C502308075	Gray	75 ft
C502308100	Gray	100 ft
C502209015	White	15 ft
C502209020	White	20 ft
C502209025	White	25 ft
C502209035	White	35 ft
C502209050	White	50 ft
C502209075	White	75 ft
C502209100	White	100 ft
C502309010	White	10 ft
C502309015	White	15 ft
C502309020	White	20 ft
C502309025	White	25 ft
C502309035	White	35 ft
C502309050	White	50 ft
C502309075	White	75 ft
C502309100	White	100 ft
C502304010	Yellow	10 ft
C502304020	Yellow	20 ft
C502304030	Yellow	30 ft
C502304040	Yellow	40 ft
C502304050	Yellow	50 ft
C502304060	Yellow	60 ft
C502304070	Yellow	70 ft

History

Update and Revision:	Revision Number: 0.47 Revision Date: 11-09-2022
----------------------	---

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.