



Product: [Cabinet Top Frame Brush Kit](#)

Product Description

Technical Specifications

Application

Environmental Space:	Indoor
----------------------	--------

Environmental and Overall Characteristics

Finish:	Powder coat Finish
Material:	Steel

Related Part Numbers

Included Parts:	Brush frame (1), Brush and Mounting Hardware
Packaging:	Individual bag, bulk packaged

Variants

Application	Item #	Description	Color
XHSN Series	HSNTBK30101	Cabinet Top Frame Knockout Brush Kit for 30"Wide XHSN	Black
XHSN Series	HSNTBK30102	Cabinet Top Frame Knockout Brush Kit for 30"Wide XHSN	White
XHSN Series	HSNTBK30201	Cabinet Top Frame Knockout Brush Kit for 30"Wide XHSN	Black
XHSN Series	HSNTBK30202	Cabinet Top Frame Knockout Brush Kit for 30"Wide XHSN	White
XHSN Series	HSNTBK40101	Cabinet Top Frame Knockout Brush Kit for 40"Wide XHSN	Black
XHSN Series	HSNTBK40102	Cabinet Top Frame Knockout Brush Kit for 40"Wide XHSN	White
XHSN Series	HSNTBK40201	Cabinet Top Frame Knockout Brush Kit for 40"Wide XHSN	Black
XHSN Series	HSNTBK40202	Cabinet Top Frame Knockout Brush Kit for 40"Wide XHSN	White
XHS Series	HSTBK30101	Cabinet Top Frame Knockout Brush Kit for 30"Wide XHS/XHSS	Black
XHS Series	HSTBK30102	Cabinet Top Frame Knockout Brush Kit for 30"Wide XHS/XHSS	White
XHS Series	HSTBK30201	Cabinet Top Frame Knockout Brush Kit for 30"Wide XHS/XHSS	Black
XHS Series	HSTBK30202	Cabinet Top Frame Knockout Brush Kit for 30"Wide XHS/XHSS	White
XHS Series	HSTBK30301	Cabinet Top Frame Knockout Brush Kit for 30"Wide XHS/XHSS	Black
XHS Series	HSTBK30302	Cabinet Top Frame Knockout Brush Kit for 30"Wide XHS/XHSS	White
XHS Series	HSTBK40101	Cabinet Top Frame Knockout Brush Kit for 40"Wide XHS/XHSS	Black
XHS Series	HSTBK40102	Cabinet Top Frame Knockout Brush Kit for 40"Wide XHS/XHSS	White
XHS Series	HSTBK40201	Cabinet Top Frame Knockout Brush Kit for 40"Wide XHS/XHSS	Black
XHS Series	HSTBK40202	Cabinet Top Frame Knockout Brush Kit for 40"Wide XHS/XHSS	White

Update and Revision:	Revision Number: 0.22 Revision Date: 04-08-2022
----------------------	---

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.