



Product: [CloudRail.Box Max](#) 

The CloudRail.Box Max acts as an Edge Gateway between the shop floor and the cloud.

Product Description

The CloudRail.Box Max supports all connectivity methods like Secondary Sensors, OPC-UA, Modbus, and VSEs. This version comes with a powerful Processor and enough storage. This makes the CloudRail.Box Max the perfect choice for advanced Edge Computing scenarios using AWS IoT Greengrass v2, Azure IoT Edge, or CloudRail Edge Functions. Moreover this version is able to connect more data sources with a single edge gateway.

Technical Specifications

Product description

Type:	CloudRail.Box Max
Part Number:	942347001
Port type and quantity:	3x RJ45
Port Speed:	2.5 GbE (I226-IT)

More Interfaces

Serial Interface:	1x RS-485 / 1x RS-232 (optional), 1x HDMI
SIM Cards:	1x Nano-SIM (4FF)
Power Supply:	4-pin terminal block with power switch function

Hardware

Bypass:	N/A
CPU:	Intel Atom® x6413E
Encryption:	TPM 2.0 (Trusted Platform Module)
Memory:	8 GB LPDDR4 RAM
Storage:	220 GB (Free Storage for Container and Data)

Power requirements

Operating Voltage:	12-24V DC
Power consumption:	min. 40W

Software

Management:	CloudRail.DMC (Device Management Cloud)
Security:	Integrated Firewall End-to-end encrypted connectivity / TPM 2.0 / Remote Security patches

Ambient conditions

Operating temperature:	-20-+60 °C
Storage/transport temperature:	-40-+85 °C
Relative humidity (non-condensing):	5-95 %

Mechanical construction

Dimensions (WxHxD):	130 mm x 90 mm x 30 mm
Weight:	500 g
Housing Material:	Steel / Aluminum
Mounting:	DIN Rail 35 mm

Approvals

Basis Standard:	CE, FCC
Safety of information technology equipment:	UL 62368-1

Scope of delivery and accessories

Scope of delivery:	1 x Device
--------------------	------------

Further Instructions

Product Documentation:	https://www.doc.hirschmann.com/index.html
Certificates:	https://www.doc.hirschmann.com/certificates.html

History

Update and Revision:	Revision Number: 0.12 Revision Date: 01-16-2025
----------------------	---

Variants

Item #	Type
942347001	CloudRail.Box Max

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.