



Product: [Connectivity Suite](#)

Secure, scalable remote-management platform with VPN, OTA, REST API, and monitoring for NetModule Routers

Product Description

Connectivity Suite by NetModule is a scalable IoT device management and remote-control platform supporting OTA updates, REST API, VPN, PKI, and monitoring.

Technical Specifications

Product description

Type:	Connectivity Suite Router Management & VPN Server
Node extension:	Supports adding devices/networks and grouping
License:	Annual license, tiered by device count (CS_20_Lic to CS_1000_Lic)
Validity:	12 months

Software

Operating system:	Ubuntu 20.04/22.04, Debian 10
Browser:	Microsoft Edge, Google Chrome, Mozilla Firefox

Hardware

Processor:	2 cores @ 2.5 GHz minimum
Hard disk space:	120GB
RAM:	16GB
Network:	Automated VPN infrastructure with encryption

SCADA /Process visualisation

OPC Server:	Not supported / N/A
-------------	---------------------

IIT.Protocols

Supported protocols:	REST API, OpenVPN, HTTPS
----------------------	--------------------------

Language Support

Manual and help texts:	English
Menus and dialogs:	English

Scope of delivery and accessories

Scope of delivery:	Software License Key, documentation, CLI tools
--------------------	--

Further Instructions

Product Documentation:	Datasheet (PDF), User Manual, Wiki, Release Notes
Certificates:	Automatic PKI certificate handling, generation and management

History

Update and Revision:	Revision Number: 0.24 Revision Date: 11-05-2025
----------------------	---

Variants

Part Number	Item Description	Type
-------------	------------------	------

942 998-681	CS_5_Free_Lic	5 licences
942 998-278	CS_20_Lic	20 licences
942 998-682	CS_50_Lic	50 licences
942 998-683	CS_100_Lic	100 licences
942 998-684	CS_200_Lic	200 licences
942 998-279	CS_300_Lic	300 licences
942 998-280	CS_400_Lic	400 licences
942 998-281	CS_500_Lic	500 licences
942 998-685	CS_600_Lic	600 licences
942 998-686	CS_700_Lic	700 licences
942 998-282	CS_800_Lic	800 licences
942 998-687	CS_900_Lic	900 licences
942 998-283	CS_1000_Lic	1000 licences

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.