



Product: [DCX-02RM-096P](#)



DCX 2U PATCH PANEL 96P 2 TRAYS EMPTY BLACK FINISH

Product Description

DCX 2U PATCH PANEL HOUSING 96-PORT (2 TRAYS) EMPTY, BLACK FINISH

Technical Specifications

Product Overview

Suitable Applications:	Optical Solutions, Backbone, Telecommunication Rooms, Main Distribution Rooms, Data Centers
------------------------	---

Construction

Weight:	15.000 lbs
Height:	3.470 in
Width:	19.000 in
Depth:	17.500 in

Physical Specifications

Max Capacity:	96 Ports (192 Fibers - LC): 8 Cassettes - Base-24 / 16 Cassettes - Base-12 / 24 Cassettes - Base-8
---------------	--

Mechanical Characteristics

Front Connection:	Static
-------------------	--------

Temperature Range

Operating Temperature Range:	-10°C to +60°C
Storage Temperature Range:	-40°C to +70°C

Product Material

Materials

Description	Material
Housing	Steel
Housing	PC/ABS
Housing	Polycarbonate

Standards

TIA/EIA Compliance:	EIA/ECA 310
MII Order #39 (China RoHS):	EUP 50

Related Part Numbers

Included Parts:	Hardware Kit (see notes)
Related Parts:	DCX Cassettes, Adapter Frames, MPO Trunks, Patch Cords

Variants

Item #	Color
DCX-02RM-096P	Black

Product Notes

Packaging:	Individually packaged in a cardboard box.
Notes:	Hardware Kit contains: Screws (12-24); Screws (10-32); Velcro cable tie; Wire marker card-blue-brady; Tie Wraps; Kurly locks; Installation guide

History

Update and Revision:	Revision Number: 0.12 Revision Date: 02-12-2025
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.