

Product: [DCX-04FM-RL](#) 



DCX 4U Housing with 12 Trays, Right-to-Left Flow

## Product Description

DCX HOUSING 4U, RIGHT-LEFT CABLE FLOW, WITH 12 TRAYS, TRUNK & PATCH MANAGEMENT

## Technical Specifications

### Product Overview

Environmental Space:	Indoor
Suitable Applications:	Optical Distribution Frame, Data Centers, Central Equipment Room

### Construction

Weight:	17.47 lbs
Height:	6.729 in
Width:	20.807 in
Depth:	11.81

### Physical Specifications

Max Capacity:	Holds 48 Cassettes/Frames, Base 12 or 72 Cassettes, Base-8
---------------	--

### Mechanical Characteristics

Termination Type:	Front and Right Trunk Cables Access
-------------------	-------------------------------------

### Temperature Range

Operating Temp Range:	-10°C To +60°C
Storage Temp Range:	-40°C To +70°C

### Product Material

#### Materials

Element	Description
Steel	Housing
PC/ABS	Housing
Polycarbonate	Housing

### Standards

MII Order #39 (China RoHS):	EUP 50
-----------------------------	--------

### Part Number

Included Parts:	#12-24 machine screw Phillips (4x). Rail cage nuts (4x)
-----------------	---

#### Variants

Item #	Color	UPC
DCX-04FM-RL	Black	611589248198

### Product Notes

Packaging:	Individually packaged in a cardboard box
------------	--

Notes: For more information, please refer to our web site at <http://www.belden.com>.

## History

Update and Revision: Revision Number: 0.80 Revision Date: 05-06-2021

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.