



Product: [FC3U06LKMFAx](#)



FXU Cassette OM3 06 Ports

Product Description

FX ULTRA CASSETTE, OM3, 06 PORTS, MPO-12 FEMALE, TYPE A LC DUPLEX KEYED

Technical Specifications

Product Overview

| | |
|------------------------|---|
| Environmental Space: | Indoor |
| Suitable Applications: | FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers |

Construction

Fiber Cable Construction

| Fiber Type | |
|------------|--------|
| OM3 | |
| Height: | 1.5 in |
| Width: | 4.5 in |
| Length: | 6.6 in |

Mechanical Characteristics

| | |
|-------------------|----------------|
| Front Connection: | 1 Inch Pullout |
|-------------------|----------------|

Temperature Range

| | |
|------------------------------|-------------|
| Operating Temperature Range: | -10 to 60°C |
| Storage Temperature Range: | -10 to 75°C |

Product Material

Materials

| Description | Material | Color | Type |
|----------------------|-------------------|-------|----------|
| Adapter Sleeve | Zirconia-Ceramic | | |
| Front Connector Body | Plastic - UL94V-0 | Red | LC Keyed |
| Cassette assy | Plastic - UL94V-0 | Black | 1.25mm |

Transmission-Characteristics

Fiber Connector Performance

| Max. Insertion Loss | Min. Return Loss |
|---------------------|------------------|
| 0.25 dB | -30 dB |
| 0.35 dB | -30 dB |

Standards

| | |
|-----------------------------------|-----|
| EU Directive 2011/65/EU (RoHS 2): | Yes |
|-----------------------------------|-----|

Related Part Numbers

| | |
|----------------|--|
| Related Parts: | FX UHD & FXU Patch Panels, FX MPO Trunks |
|----------------|--|

Variants

| Item # | Connector Type |
|---------------|-----------------|
| FC3U06LKMFAA | LC Keyed Aqua |
| FC3U06LKMFAB | LC Keyed Blue |
| FC3U06LKM FAG | LC Keyed Green |
| FC3U06LKM FAM | LC Keyed Brown |
| FC3U06LKM FAN | LC Keyed Black |
| FC3U06LKM FAO | LC Keyed Orange |
| FC3U06LKM FAP | LC Keyed Rose |
| FC3U06LKM FAR | LC Keyed Red |
| FC3U06LKM FAS | LC Keyed Gray |
| FC3U06LKM FAV | LC Keyed Violet |
| FC3U06LKM FAW | LC Keyed White |
| FC3U06LKM FAY | LC Keyed Yellow |

Product Notes

| | |
|------------|---|
| Packaging: | Individually packaged in a plastic shell, Shipped in cardboard box (14/box) |
|------------|---|

History

| | |
|----------------------|--|
| Update and Revision: | Revision Number: 0.2 Revision Date: 05-09-2025 |
|----------------------|--|

© 2025 Belden, Inc
 All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.