

**Product:** [FCSX12SBMF](#) 

FX ECX CASS OS2 12P MPO12(F) SC\_SX/APC TYPE-A GN\_ADP



**Product Description**

FX ECX CASSETTE, OS2, 12 PORTS, MPO-12 (FEMALE), SC SIMPLEX/APC, TYPE-A, GREEN ADAPTERS

**Technical Specifications**

**Product Overview**

Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers
------------------------	---

**Construction**

Weight:	0.500 lbs
Height:	1.290 in.
Width:	6.340 in
Depth:	8.685 in

**Physical Specifications**

Max Capacity:	12 Fibers
---------------	-----------

**Temperature Range**

Operating Temp Range:	-10°C to +60°C
Storage Temp Range:	-10°C to +75°C

**Product Material**

**Materials**

Description	Material	Color	Type
Front Connector/Adapter	Plastic - UL94V-0	Green	SC/APC Simplex
Rear Connector/Adapter	Plastic - UL94V-0	Green	MPO Female
Cassette Assembly	PC/ABS	Black	

**Standards**

MII Order #39 (China RoHS):	EUP 50
-----------------------------	--------

**Related Part Numbers**

Related Parts:	FX ECX Patch Panels, Patch Cords, MPO Trunks
----------------	--

**Product Notes**

Packaging:	Individually packaged in a plastic shell, Shipped in cardboard box
Notes:	For more information, please refer to our website at <a href="http://www.belden.com">http://www.belden.com</a>

**History**

Update and Revision:	Revision Number: 0.6 Revision Date: 04-08-2022
----------------------	--

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.