

Product: [FDSM012P2](#) 

Indoor/Outdoor Plenum OS2 Mini-Distribution 12 Fibers 3mm SubUnit



Product Description

FX Indoor/Outdoor, OS2, Mini-Distribution, 12 Fibers, OFNP, 12F/Sub-Unit (3.00mm), Black Jacket

Technical Specifications

Product Overview

Product Category:	Fiber Mini Distribution Cable
Suitable Applications:	Data Center, RAN, Horizontal Backbone, Premise Backbone, Patching, Trunking

Fiber Specifications

Fiber Type:	OS2
Fiber Core Diameter:	8.2/125 μ m
Fiber Diameter:	250 μ m
Fiber Count:	12
Fiber Color Coding:	TIA-598-D

Inner Jacket Specifications

Inner Jacket Strength Member:	Aramid Yarns
Material:	PVC - Polyvinyl Chloride
Nominal Diameter@InnerJacket1 (cnv):	0.130 in (3.3 mm)
Color:	Yellow
Number of Inner Jacket Ripcords:	1

Outer Jacket Specifications

Strength Member:	Aramid Yarns
Jacket Material:	PVC - Polyvinyl Chloride
Nom. Diameter:	0.265 in (6.7 mm)
Outer Jacket Color:	Black
Outer Jacket Ripcord:	1

Optical Characteristics

Wavelength	1310 nm	1550 nm
Max. Attenuation	0.5 dB/km	0.50 dB/km

Mechanical Characteristics

Minimum Bend Radius During Installation:	15x Cable OD
Minimum Bend Radius During Operation:	10x Cable OD
Max. Tensile Strength During Installation:	1320 N (300 lbf)
Max. Tensile Strength During Operation:	400 N (90 lbf)
Crush Resistance:	110 N/cm
Bulk Cable Weight:	33 lbs/kft (49 kg/km)

Temperature Range

Installation Temperature Range:	0°C to +60°C
---------------------------------	--------------

Operating Temperature Range:	-20°C to +70°C
Storage Temperature Range:	-20°C to +70°C

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Sunlight Resistance, UV Resistance, Burial
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	OFNP, UL 910, FT6
NEC / UL Compliance:	OFNP
CEC / C(UL) Compliance:	OFNP
ICEA Compliance:	S-104-696
TIA/EIA Compliance:	ANSI/ICEA S-104-696
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

History

Update and Revision:	Revision Number: 0.68 Revision Date: 09-07-2025
----------------------	---

Part Numbers

Variants

Item #	Color
FDSM012P2A	Aqua
FDSM012P2E	Erika Violet
FDSM012P2L	Lime Green
FDSM012P2O	Orange
FDSM012P2Y	Yellow

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.