

Product: [FF4D04MP](#) 



FX DCX FRAME, OM4, 04 PORTS, MPO KEY UP/KEY DOWN

Product Description

FX DCX FRAME, OM4, 04 PORTS, MPO KEY UP/KEY DOWN, ERIKA VIOLET ADAPTERS

Technical Specifications

Part Number:	FF4D04MP
--------------	----------

Product Overview

Environmental Space:	Indoor
Suitable Applications:	Optical Distribution Frame, Data Centers, Central Equipment Room

Construction

Fiber Cable Construction

Fiber Type	OM4
Weight:	0.066 lbs
Height:	0.448 in
Width:	2.260 in
Depth:	5.7 in

Temperature Range

Operating Temp Range:	-10 to 60°C
Storage Temp Range:	-10 to 75°C

Product Material

Materials

Description	Material	Color
Frame	Plastic - UL94V-0	Black
Front Connector Body	Plastic - UL94V-0	Erika Violet

Standards

EU RoHS Compliance Date (yyyy-mm-dd):	2013-01-11
MII Order #39 (China RoHS):	EUP 50

Additional Notes

Packaging:	Individually packaged in a plastic shell, Shipped in cardboard box
Related Parts:	DCX Frame Module & Patch Panel

History

Variants

Item #	Color	Connector Type	Port Count	Fiber Type
FF4D04MP	Erika Violet	MPO Male	4 Port	OM4

Update and Revision:	Revision Number: 0.17 Revision Date: 04-27-2020
----------------------	---

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.