



Product: [FX UHD Bezel Panel 1U](#)

FiberExpress Ultra HD Bezel Panel 1U

Product Description

FX UHD Bezel Panel 1U (For up to 4 Modules or 72 Ports)

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers

Construction

Weight:	0.840 lbs
Height:	1.625 in
Width:	19 in
Depth:	1.0 in

Physical Specifications

Max Capacity Table

	Quantity of Frames/Cassettes	Quantity of LC Duplex Connectors
FX UHD Frames/Cassettes	4	72
FX Ultra Frames/Cassettes	4	48
Max Capacity:	1U FiberExpress Ultra HD Patch Panel STD & RECS Shelf	

Mechanical Characteristics

Termination Style:	Static FXU HD / 1inch Pullout FXU
--------------------	-----------------------------------

Temperature Range

Operating Temperature Range:	-10°C To +60°C
Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C

Product Material

Materials

Description	Material
Panel	Steel

Standards

MII Order #39 (China RoHS):	EUP 50
-----------------------------	--------

Related Part Numbers

Included Parts:	Screws (12-24); Screws (10-32); Velcro Straps; Identification Labels
Related Parts:	FiberExpress Ultra and Ultra High Density Frames and Cassettes

Variants

Item #	Color
AX105812	Black
AX105813	Titanium

Product Notes

Packaging:	Individually packaged in a cardboard box
Notes:	For more information, please refer to Installation Guide: PX105797

History

Update and Revision:	Revision Number: 0.56 Revision Date: 11-09-2022
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.