



**Product:** [FX UHD Frame LC Duplex](#)

FX UHD LC Duplex Frame, 6-18 Ports

### Product Description

FX UHD Frame LC Duplex. Available in multiple fiber types and port counts.

### Technical Specifications

#### Product Overview

Environmental Space:	Indoor
Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers

#### Construction

Weight:	0.25 lbs
Height:	1.5 in
Width:	4.46 in
Depth:	2.2 in

#### Temperature Range

Operating Temperature Range:	-10 to 60°C
Storage Temperature Range:	-10 to 75°C

#### Product Material

##### Materials

Description	Material	Color	Type
Frame	Plastic - UL94V-0	Black	
Front Connector Body	Plastic - UL94V-0		LC Duplex

#### Standards

MII Order #39 (China RoHS):	EUP 50
-----------------------------	--------

#### Related Part Numbers

Included Parts:	Dust Caps
Related Parts:	FiberExpress Ultra Patch panels, Pre-terminated MPO low loss cable assemblies

##### Variants

Item #	Color	Connector Type	Port Count	Fiber Type
FF3H18LD	Aqua	LC Duplex	18 Port	OM3
FF3H12LD	Aqua	LC Duplex	12 Port	OM3
FF3H06LD	Aqua	LC Duplex	6 Port	OM3
FFSH18LD	Blue	LC Duplex	18 Port	OS2
FFSH12LD	Blue	LC Duplex	12 Port	OS2
FFSH06LD	Blue	LC Duplex	6 Port	OS2
FF4H18LD	Erika Violet	LC Duplex	18 Port	OM4
FF4H12LD	Erika Violet	LC Duplex	12 Port	OM4

#### Product Notes

Packaging:	Individually packaged in a plastic shell. Shipped in cardboard box (60/box)
------------	---

**History**

Update and Revision:	Revision Number: 0.53 Revision Date: 04-08-2022
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.